



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TB750S 1/2 3G Bell Box *Hubbell--Raco*

| | |
|------------------|--------------------------------------|
| Catalog Number | TB750S |
| Manufacturer | Hubbell--Raco |
| Description | 3G WP Box (7) 1/2 In. Outlets - Gray |
| Weight per unit | 1.3 (lbs/each) |
| Product Category | Outlet Boxes, Etc. - Steel |

Features

| | |
|------------------|----------------|
| Knockouts | 1/2 IN Holes;7 |
| Material | Metal |
| number of outlet | 7 |

Material, Color, and Finish

| | |
|-------|------|
| Color | Gray |
|-------|------|

Dimensions and Weight

| | |
|------|--------|
| Size | 3-Gang |
|------|--------|

Descriptions

| | |
|------------------------|--|
| Construction | Die Cast |
| Description | 1/2 3G BELL BOX |
| extra long description | RACO TB750S 3-G GY WP Box with Seve |
| Long Description | 3G WP BOX (7) 1/2 IN. OUTLETS - GRAY |
| Product Type | 3-G Gy WP Box With Seven 1/2 In. Outlets |
| Special Features | TAYMAC Weatherproof outlet boxes are made of superior commercial quality die cast metal construction and are finished with a premium powdercoat. NEMA 3R compliant; 3 gang; includes closure plugs, grounding screw, and mounting hardware; white. |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Taymac |
| GTIN | 00092326112642 |
| Manufacturers Part Number | TB750S |
| UPC | 092326112642 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | WEATHERPROOF BOXES & COVERS |
| Type | 3-Gang Seven Hole Outlet Box - 1/2 IN Holes |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Weight Per each | 1.34 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------|------------|
| Application | Electrical |
| standard | UL |