



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



THHN20RD2500 THHN 2/0 STR Red 2500' *Southwire Company*

| | |
|------------------|--|
| Catalog Number | THHN20RD2500 |
| Manufacturer | Southwire Company |
| Description | 600 Volts. Copper Conductor. Thermoplastic Insulation/Nylon Sheath, Heat, Moisture, Gasoline and Oil Resistant li. Rated THHN and THWN-2. Also Rated MTW. Simpull Technology For Easier Pulling. |
| Weight per unit | 0.4620 (lbs/ft) |
| Product Category | Wire |

Features

| | |
|----------------------|-----|
| Conductor Size | 2/0 |
| media | Yes |
| Number of Conductors | 1 |
| Voltage Rating | 600 |

Material, Color, and Finish

| | |
|---------------------|-------|
| Insulation Material | PVC |
| Jacket Material | Nylon |

Dimensions and Weight

| | |
|--------|------|
| Length | 2500 |
|--------|------|

Descriptions

| | |
|------------------------|--|
| Description | THHN 2/0 STR RED 2500' |
| extra long description | SWC 55611304 THHN 2/0 Str Cu SIM Rd |
| Long Description | 600 Volts. Copper Conductor. Thermoplastic Insulation/Nylon Sheath, Heat, Moisture, Gasoline and Oil Resistant II. Rated THHN and THWN-2. Also rated MTW. SIMpull Technology for Easier Pulling. |
| Product Type | THHN 2/0 STR Cu Sim RD 2500R |
| Special Features | No Lube |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Copper |
| GTIN | 00032886913570 |
| Manufacturers Part Number | 55611304 |
| UPC | 032886913570 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------|
| Category Description | BUILDING WIRE |
| Type | THHN-2 |

Availability

| | |
|-------------|------|
| minimum qty | 2500 |
|-------------|------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton 2500

Weight Per foot 0.462

Uses, Certifications, and Standards

Application Commerical