



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## THQL1130 1P 30A 120/240V Circuit Breaker

*Industrial Connections &*

Catalog Number	THQL1130
Manufacturer	Industrial Connections &
Description	Q Line Circuit Breakers Are One-Inch Wide Per Pole, Compact, Thermal-Magnetic Devices Designed For Residential and Commercial Applications In Load Centers or Lighting Panels. All Q Line Circuit Breakers Feature Quick-Make / Quick-Break Mechanisms, Common Trip Bars, and Easy to Spot Trip Indication to Ensure Safety and Reliability. Q Line Breakers Can Be Ordered With Auxiliary Contact and Shunt Trip Accessories, and Can Be Ordered For Use In Hid Applications. The THQL1130 Breaker Features 1 Pole, An Ampere
Weight per unit	312.0 (lbs/each)
Product Category	1 Pole Standard Trip Plug-In

### Features

amperage rating	30 A
circuit breaker type	Residential
frame	Q-Line
interrupt rating	10kA@120 Vac / 10kA@120/240 Vac
Load Rating	HACR
media	Yes
Poles	1
trip range	Non-Interchangeable
Trip Type	LI
Voltage Rating	120/240 V



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	1P 30A 120/240V CIRCUIT BREAKER
extra long description	GE THQL1130 THQL 1 POLE 120/240V 10
Long Description	Q Line circuit breakers are one-inch wide per pole, compact, thermal-magnetic devices designed for residential and commercial applications in load centers or lighting panels. All Q Line circuit breakers feature Quick-make / Quick-break mechanisms, common trip bars, and easy to spot trip indication to ensure safety and reliability. Q Line breakers can be ordered with auxiliary contact and shunt trip accessories, and can be ordered for use in HID applications. The THQL1130 breaker features 1 pole, an ampere
Product Type	THQL 1 Pole 120/240V 10K Ic 30amp
Special Features	Q Line circuit breakers are one-inch wide per pole, compact, thermal-magnetic devices designed for residential and commercial applications in load centers or lighting panels. All Q Line circuit breakers feature Quick-make / Quick-break mechanisms, common trip bars, and easy to spot trip indication to ensure safety and reliability. Q Line breakers can be ordered with auxiliary contact and shunt trip accessories, and can be ordered for use in HID applications. The THQL1130 breaker features 1 pole, an ampere

## Manufacturer Information

Brand	GE
GTIN	00783164012873
Manufacturers Part Number	THQL1130
UPC	783164012873

## Taxonomies, Classifications, and Categories

Category Description	Loadcenter Plug In Breakers and Accessories
Type	Q-Line Plug-In

## Packaging

Carton	10
Package	1
Weight Per each	312

## Uses, Certifications, and Standards

Application	Thermal Magnetic
standard	E11592