



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## THQL32040 3P 40A 240V Plug-In Circuit Breaker

*Industrial Connections &*

Catalog Number	THQL32040
Manufacturer	Industrial Connections &
Description	Q Line Circuit Breakers Are One-Inch Wide Per Pole, Compact, Thermal-Magnetic Devices Designed For Residential and Commercial Applications In Load Centers or Lighting Panels. All Q Line Circuit Breakers Feature Quick-Make / Quick-Break Mechanisms, Common Trip Bars, and Easy to Spot Trip Indication to Ensure Safety and Reliability. Q Line Breakers Can Be Ordered With Auxiliary Contact and Shunt Trip Accessories, and Can Be Ordered For Use In Hid Applications. The THQL32040 Breaker Features 3 Poles, An Amper
Weight per unit	1,106.0 (lbs/each)
Product Category	3 Pole Standard Trip Plug-In

### Features

amperage rating	40 A
frame	Q-Line
interrupt rating	10kA@120 Vac / 10kA@120/240 Vac / 10kA@240 Vac
Load Rating	HACR
Poles	3
trip range	Non-Interchangeable
Trip Type	LI
Voltage Rating	240 V



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	3P 40A 240V PLUG-IN CIRCUIT BREAKER
extra long description	GE THQL32040 CIRCUIT BREAKER 3P 40
Long Description	Q Line circuit breakers are one-inch wide per pole, compact, thermal-magnetic devices designed for residential and commercial applications in load centers or lighting panels. All Q Line circuit breakers feature Quick-make / Quick-break mechanisms, common trip bars, and easy to spot trip indication to ensure safety and reliability. Q Line breakers can be ordered with auxiliary contact and shunt trip accessories, and can be ordered for use in HID applications. The THQL32040 breaker features 3 poles, an amper
Product Type	Circuit Breaker 3P 40A 240 10ka
Special Features	Q Line circuit breakers are one-inch wide per pole, compact, thermal-magnetic devices designed for residential and commercial applications in load centers or lighting panels. All Q Line circuit breakers feature Quick-make / Quick-break mechanisms, common trip bars, and easy to spot trip indication to ensure safety and reliability. Q Line breakers can be ordered with auxiliary contact and shunt trip accessories, and can be ordered for use in HID applications. The THQL32040 breaker features 3 poles, an amper

## Manufacturer Information

Brand	GE
GTIN	00783164013030
Manufacturers Part Number	THQL32040
UPC	783164013030

## Taxonomies, Classifications, and Categories

Category Description	MOLDED CASE BREAKERS
----------------------	----------------------

## Packaging

Carton	1
Weight Per each	1106

## Uses, Certifications, and Standards

Application	Thermal Magnetic
standard	E11592