



# Decorator Devices TradeMaster® Decorator Combination Switches

15A, 120/125VAC



TM818-WCC



TM8118-WCC

Catalog Number	Rating A. VAC	Color	NEMA Config. No.	3rd Party Compliance		
				UL <sub>20</sub>	UL <sub>498</sub>	cUL <sub>us</sub>
<b>Single Pole Switch &amp; Single Receptacle</b>						
TM818-ICC	15 120/125	Ivory	5-15R	•	•	•
TM818-WCC	15 120/125	White	5-15R	•	•	•
TM818-BKCC	15 120/125	Black	5-15R	•	•	•
TM818-LACC	15 120/125	Light Almond	5-15R	•	•	•
<b>Single Pole Switch &amp; Single Receptacle with Pilot Light</b>						
TM818-PLICC	15 120/125	Ivory	5-15R	•	•	•
TM818-PLWCC	15 120/125	White	5-15R	•	•	•
TM818-PLBKCC	15 120/125	Black	5-15R	•	•	•
TM818-PLLACC	15 120/125	Light Almond	5-15R	•	•	•
<b>Three-Way Switch &amp; Single Receptacle</b>						
TM838-ICC	15 120/125	Ivory	5-15R	•	•	•
TM838-WCC	15 120/125	White	5-15R	•	•	•
TM838-BKCC	15 120/125	Black	5-15R	•	•	•
TM838-LACC	15 120/125	Light Almond	5-15R	•	•	•
<b>Two Single Pole Switches &amp; Single Receptacle</b>						
TM8118-ICC	15 120/125	Ivory	5-15R	•	•	•
TM8118-WCC	15 120/125	White	5-15R	•	•	•
TM8118-BKCC	15 120/125	Black	5-15R	•	•	•
TM8118-LACC	15 120/125	Light Almond	5-15R	•	•	•
<b>Single Pole Switch &amp; Pilot Light</b>						
TM81-PLICC	15 120/125	Ivory		•	•	•
TM81-PLWCC	15 120/125	White		•	•	•
TM81-PLBKCC	15 120/125	Black		•	•	•
TM81-PLLACC	15 120/125	Light Almond		•	•	•
<b>Three-Way Switch &amp; Pilot Light</b>						
TM83-PLICC	15 120/125	Ivory		•	•	•
TM83-PLWCC	15 120/125	White		•	•	•
TM83-PLBKCC	15 120/125	Black		•	•	•
TM83-PLLACC	15 120/125	Light Almond		•	•	•

**Features**

- No tool needed, module snaps-in.
- Lights when OFF.
- Uses energy-efficient 1/4 watt LED light.
- LED light will not generate heat and will last on average 47 years.
- Can be installed with the following devices: TM811, TM813, TM833, TM818, TM838, TM8111, TM8113, TM81111 and TM8118.

Catalog Number	Rating A. VAC	Color	NEMA Config. No.	3rd Party Compliance		
				UL <sub>20</sub>	UL <sub>498</sub>	cUL <sub>us</sub>
<b>Snap-In Light Module</b>						
TM8LM	15 120/125	Clear		•	•	



For Decorator Hallway Light and Single Receptacle and Full Hallway Light, see Pages D-12 and R-32.

# Decorator Devices TradeMaster® Decorator Combination Switches

15A, 120/277VAC


Pass & Seymour  
legrand®

Decorator Devices


## Features

- Impact-resistant face and body.
- Fully rounded back body protects wires from being damaged by sharp edges.
- Clear identification of circuits.
- External screw-pressure-plate back and side wired. Accepts #12 and #14 AWG.
- Ground screw position under the end of the strap minimizes the risk of contact.
- Full wrap around metal strap with lock-in tabs.
- Patented split circuit tab – easily accessible, and can be reinstalled without a tool.
- Unique “Up/Down” switches match the look and feel of standard Decorator switches.
- Largest 15 amp offering.
- All screws are tri-drive.
- Patented Snap-In Light Module (sold separately).


Catalog Number	Rating A. VAC	Color	3rd Party Compliance	
			UL UL20	UL cULus
<b>Two Single Pole Switches</b>				
TM811-ICC	15 120/277	Ivory	•	•
TM811-WCC	15 120/277	White	•	•
TM811-BKCC	15 120/277	Black	•	•
TM811-LACC	15 120/277	Light Almond	•	•
<b>Two Single Pole Switches with Pilot Light</b>				
TM811-PLICC	15 120/277	Ivory	•	•
TM811-PLWCC	15 120/277	White	•	•
TM811-PLBKCC	15 120/277	Black	•	•
TM811-PLLACC	15 120/277	Light Almond	•	•
<b>Single Pole Switch &amp; Three-Way Switch</b>				
TM813-ICC	15 120/277	Ivory	•	•
TM813-WCC	15 120/277	White	•	•
TM813-BKCC	15 120/277	Black	•	•
TM813-LACC	15 120/277	Light Almond	•	•
<b>Single Pole Switch &amp; Three-Way Switch with Pilot Light</b>				
TM813-PLICC	15 120/277	Ivory	•	•
TM813-PLWCC	15 120/277	White	•	•
TM813-PLBKCC	15 120/277	Black	•	•
TM813-PLLACC	15 120/277	Light Almond	•	•
<b>Two Three-Way Switches</b>				
TM833-ICC	15 120/277	Ivory	•	•
TM833-WCC	15 120/277	White	•	•
TM833-BKCC	15 120/277	Black	•	•
TM833-LACC	15 120/277	Light Almond	•	•
<b>Three Single Pole Switches</b>				
TM8111-ICC	15 120/277	Ivory	•	•
TM8111-WCC	15 120/277	White	•	•
TM8111-BKCC	15 120/277	Black	•	•
TM8111-LACC	15 120/277	Light Almond	•	•
<b>Two Single Pole Switches &amp; Three-Way Switch</b>				
TM8113-ICC	15 120/277	Ivory	•	•
TM8113-WCC	15 120/277	White	•	•
TM8113-BKCC	15 120/277	Black	•	•
TM8113-LACC	15 120/277	Light Almond	•	•
<b>Four Single Pole Switches</b>				
TM81111-ICC	15 120/277	Ivory	•	•
TM81111-WCC	15 120/277	White	•	•
TM81111-BKCC	15 120/277	Black	•	•
TM81111-LACC	15 120/277	Light Almond	•	•



TM811-WCC



TM8111-WCC



TM81111-WCC

All devices listed on this page conform to NEMA WD-1.

TradeMaster® Decorator Combination Switches