



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TMCX7247 2-1/2" Cord Grips *Crouse-Hinds*

Catalog Number	TMCX7247
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series TMCX Cable Gland, Metal-Cladcorrugated, Teck Armoured and Tray Cable, Armoured Barrier and Non-Armoured Barrier, Aluminum, Outer Sheath:1.99-2.72", 2-1/2" NPT, Armor Range:1.93-2.47"
Weight per unit	4.5 (lbs/each)
Product Category	BX, MC, Armored Cable Fittings

Features

connection	Male NPT
dimensions	7.5000 IN X 4.0000 IN X 4.0000 IN
Material	Aluminum Body, Neoprene Seal

Dimensions and Weight

Size	2-1/2 in
------	----------

Descriptions

Description	2-1/2" CORD GRIPS
extra long description	CRS-H TMCX7247 2 1/2 FT MC CAB ARMO
Features	For use with metal-clad, non-armoured and tray cable, TMCX cable fittings are installed to provide a means for terminating cable at junction boxes, control centers, panelboards and enclosures for motor control and electrical distribution. They are used to form a mechanical watertight connection and to provide ground continuity of cable armour. Applied in Division 1 locations and when a seal is required.
Long Description	Eaton Crouse-Hinds series TMCX cable gland,Metal-cladcorrugated,TECK armoured and tray cable,Armoured barrier and non-armoured barrier, Aluminum, Outer Sheath:1.99-2.72", 2-1/2" NPT,Armor Range:1.93-2.47"
Product Type	2 1/2 FT MC Cab Armor Od 1.93-2.47
Special Features	Armoured/Non-Armoured Barrier Gland

Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00782274414737
Manufacturers Part Number	TMCX7247
UPC	782274414737

Taxonomies, Classifications, and Categories

Category Description	CORD CONNECTORS & CORD GRIPS
Type	Cable gland



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	4.5

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
Enclosure standard	IP56, Class I Div 1 Group A B C D, Class II, Class III
Temperature Rating	UL (CANADA AND US), CUL -25 To 60 Deg C