



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TMCX9352 3-1/2" Armored Cable Gland (2.95-3.52)

Crouse-Hinds

Catalog Number	TMCX9352
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series TMCX Cable Gland, Metal-Cladcorrugated, Teck Armoured and Tray Cable, Armoured Barrier and Non-Armoured Barrier, Aluminum, Outer Sheath:3.02-3.78", 3-1/2" NPT, Armor Range:2.95-3.52"
Weight per unit	7.9 (lbs/each)
Product Category	BX, MC, Armored Cable Fittings

Features

connection	Male NPT
dimensions	9.3800 IN X 5.3800 IN X 5.3800 IN
Material	Aluminum Body, Copper Plated Stainless Steel Spring, Neoprene Seal

Dimensions and Weight

Size	3-1/2 in
------	----------

Descriptions

Description	3-1/2" ARMORED CABLE GLAND (2.95-3.52)
extra long description	CRS-H TMCX9352 3 1/2 FT MC CAB ARMO
Features	For use with metal-clad, non-armoured and tray cable, TMCX cable fittings are installed to provide a means for terminating cable at junction boxes, control centers, panelboards and enclosures for motor control and electrical distribution. They are used to form a mechanical watertight connection and to provide ground continuity of cable armour. Applied in Division 1 locations and when a seal is required.
Long Description	Eaton Crouse-Hinds series TMCX cable gland,Metal-cladcorrugated,TECK armoured and tray cable,Armoured barrier and non-armoured barrier, Aluminum, Outer Sheath:3.02-3.78", 3-1/2" NPT,Armor Range:2.95-3.52"
Product Type	3 1/2 FT MC Cab Armor Od 2.95-3.52
Special Features	Armored/Non-Armored Gland, Cord Size 2.950 To 3.520 In

Manufacturer Information

Brand	Eaton
GTIN	00782274414751
Manufacturers Part Number	TMCX9352
UPC	782274414751



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	CORD CONNECTORS & CORD GRIPS
Type	Cable gland

Packaging

Carton	1
Weight Per each	7.9

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
Enclosure standard	IP56
Temperature Rating	UL (CANADA AND US), CUL
	-25 To 60 Deg C