



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TP1610F Vinylug Fork 22-16, 8-10 *Burndy LLC*

Catalog Number	TP1610F
Manufacturer	Burndy LLC
Description	Fork Tongue Copper Terminal, 22-16 Max. Insul. Dia. Accom.: .145 Color Code: Red, 8-10, .95 In L, .41 In W, Polyvinylchloride Insulation.
Weight per unit	0.0020 (lbs/each)
Product Category	Small Terminals & Connectors

Features

insulation	Y
Insulation Type	Vinyl
Material	Copper
pallet quantity	99999

Material, Color, and Finish

Color Code	RED
------------	-----

Descriptions

Description	VINYLUG FORK 22-16, 8-10
extra long description	BUR TP1610F FORK- 22- 16 AWG- VINY
Long Description	Fork Tongue Copper Terminal, 22-16 Max. Insul. Dia. Accom.: .145 Color Code: Red, 8-10, .95 in L, .41 in W, Polyvinylchloride Insulation.
Product Type	Terminal
Special Features	Features: The Type TP-F Is A Fork Tongue Variation Of The TP Design And Makes Installation Easier, 600 V Maximum, 105 DEG C Max, Fork Tongue Design: Faster Installation-Screw Needs Only To Be Loosened For Termination, Installation Tool: Plier Type: Y10-22 Tool, Ratchet: MR8-89-1 Tool, Insulation Diameter (maximum): 0.145 IN, Bulk Catalog Number: BA16EF10, Tape Mounted Catalog Number: BA16EF10M, Temperature Rating: 105 DEG C Maximum, Color Code: Red, Wire Strip Length: 13/64 IN, Finish: Electro-Tin Plated,

Manufacturer Information

Brand	BURNDY
GTIN	00781810714881
Manufacturers Part Number	TP1610F
UPC	781810714881

Taxonomies, Classifications, and Categories

Category Description	TERMINALS
Type	TP-F



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	100
--------	-----

Weight Per each	0.002
-----------------	-------

Uses, Certifications, and Standards

Application	For Commercial And Light Duty Industrial Control And Power Circuit Applications
-------------	--