

Specifications



Eaton TP292

Eaton Crouse-Hinds series Octagon Outlet Box, (3) 1/2", (2) 3/4", 4", Conduit (no clamps), 2-1/8", Steel, (2) 1/2", (2) 3/4", Fixture rated, 21.5 cubic inch capacity

General specifications

| | |
|-----------------------------|--|
| PRODUCT NAME | Eaton Crouse-Hinds series octagon outlet box |
| CATALOG NUMBER | TP292 |
| UPC | 786189102925 |
| PRODUCT LENGTH/DEPTH | 4 in |
| PRODUCT HEIGHT | 2.13 in |
| PRODUCT WIDTH | 4 in |
| PRODUCT WEIGHT | 0.64 lb |



Powering Business Worldwide

Certifications and compliances

| | |
|---------------------|----------------------------------|
| AREA CLASSIFICATION | Ordinary/Non-Hazardous Locations |
| STANDARDS TYPE | NEC/CEC |

Product specifications

| | |
|------------------|------------------------|
| BOX SIZE | 4" |
| DEPTH | 2-1/8" |
| CAPACITY | 21.5 cubic in |
| CONDUIT/CABLE | Conduit (no clamps) |
| SIDE KNOCKOUTS | (2) 1/2 in, (2) 3/4 in |
| BOTTOM KNOCKOUTS | (3) 1/2 in, (2) 3/4 in |
| MATERIAL | Steel |
| SPECIAL FEATURES | Fixture rated |

Resources

| | |
|----------|---|
| CATALOGS | Crouse-Hinds series Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans catalog page |
|----------|---|

| | |
|-----------------------|--|
| CERTIFICATION REPORTS | Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans Canadian certification Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans UL certification |
|-----------------------|--|

| | |
|-------------------------------|--|
| SPECIFICATIONS AND DATASHEETS | Steel Outlet Boxes for Electrical Systems Eaton Specification Sheet - TP292 |
|-------------------------------|--|

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.

Specifications



Eaton TP292

Eaton Crouse-Hinds series Octagon Outlet Box, (3) 1/2", (2) 3/4", 4", Conduit (no clamps), 2-1/8", Steel, (2) 1/2", (2) 3/4", Fixture rated, 21.5 cubic inch capacity

General specifications

| | |
|-----------------------------|--|
| PRODUCT NAME | Eaton Crouse-Hinds series octagon outlet box |
| CATALOG NUMBER | TP292 |
| UPC | 786189102925 |
| PRODUCT LENGTH/DEPTH | 4 in |
| PRODUCT HEIGHT | 2.13 in |
| PRODUCT WIDTH | 4 in |
| PRODUCT WEIGHT | 0.64 lb |



Powering Business Worldwide

Certifications and compliances

| | |
|---------------------|----------------------------------|
| AREA CLASSIFICATION | Ordinary/Non-Hazardous Locations |
| STANDARDS TYPE | NEC/CEC |

Product specifications

| | |
|------------------|------------------------|
| BOX SIZE | 4" |
| DEPTH | 2-1/8" |
| CAPACITY | 21.5 cubic in |
| CONDUIT/CABLE | Conduit (no clamps) |
| SIDE KNOCKOUTS | (2) 1/2 in, (2) 3/4 in |
| BOTTOM KNOCKOUTS | (3) 1/2 in, (2) 3/4 in |
| MATERIAL | Steel |
| SPECIAL FEATURES | Fixture rated |

Resources

| | |
|----------|---|
| CATALOGS | Crouse-Hinds series Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans catalog page |
|----------|---|

| | |
|-----------------------|--|
| CERTIFICATION REPORTS | Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans Canadian certification Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans UL certification |
|-----------------------|--|

| | |
|-------------------------------|--|
| SPECIFICATIONS AND DATASHEETS | Steel Outlet Boxes for Electrical Systems Eaton Specification Sheet - TP292 |
|-------------------------------|--|

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.