



TOGGLE SWITCH OPENINGS, TWO GANG, LIGHT ALMOND

TP2LA | [Pass & Seymour](#)

FEATURES & BENEFITS

Trademaster Wall Plate, two gang and toggle plate, is molded of rugged, practically indestructible self-extinguishing nylon. It is preferred for hospital, industrial, institutional, and other high-abuse applications. Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond.



- Available in "TP" series, extra 3/16 inch width and height than Standard size plates; and "TPJ" series, extra 3/16 inch width and height than Junior-Jumbo size plates.
- Nominal thickness, .070 inch.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: Light Almond
Size: Standard
Type: Toggle

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Standard: Yes
Federal Spec: No
UL Listing No: UL514
UL Standard: Yes
UN SPSC: 39121704

TECHNICAL INFORMATION

Material: Plastic

Capacity: 2-gang

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA

Buy American Act Status: Buy American Act Compliant





TOGGLE SWITCH OPENINGS, TWO GANG, LIGHT ALMOND

TP2LA | [Pass & Seymour](#)

FEATURES & BENEFITS

Trademaster Wall Plate, two gang and toggle plate, is molded of rugged, practically indestructible self-extinguishing nylon. It is preferred for hospital, industrial, institutional, and other high-abuse applications. Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond.



- Available in "TP" series, extra 3/16 inch width and height than Standard size plates; and "TPJ" series, extra 3/16 inch width and height than Junior-Jumbo size plates.
- Nominal thickness, .070 inch.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: Light Almond
Size: Standard
Type: Toggle

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Standard: Yes
Federal Spec: No
UL Listing No: UL514
UL Standard: Yes
UN SPSC: 39121704

TECHNICAL INFORMATION

Material: Plastic

Capacity: 2-gang

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA

Buy American Act Status: Buy American Act Compliant

