

# Specifications

## Eaton TP301

Eaton Crouse-Hinds series Ceiling Fan Box, (3) 1/2", 4", 1/2", Steel, Fan rated, fixture rated, 6.0 cubic inch capacity

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series ceiling fan box
<b>CATALOG NUMBER</b>	TP301
<b>UPC</b>	786189103014
<b>PRODUCT LENGTH/DEPTH</b>	4 in
<b>PRODUCT HEIGHT</b>	0.5 in
<b>PRODUCT WIDTH</b>	4 in
<b>PRODUCT WEIGHT</b>	0.51 lb



### Certifications and compliances

<b>AREA CLASSIFICATION</b>	Ordinary/Non-Hazardous Locations
<b>STANDARDS TYPE</b>	NEC/CEC

### Product specifications

<b>BOX SIZE</b>	4"
<b>DEPTH</b>	1/2"
<b>CAPACITY</b>	6 cubic in
<b>BOTTOM KNOCKOUTS</b>	(3) 1/2 in
<b>MATERIAL</b>	Steel
<b>SPECIAL FEATURES</b>	Fan rated, fixture rated

### Resources

<b>CATALOGS</b>	<a href="#">Crouse-Hinds series Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans catalog page</a>
-----------------	---

**CERTIFICATION  
REPORTS**

[Steel Octagon Boxes, Covers,  
Adjustable Bar Hangers and  
Ceiling Pans Canadian  
certification](#)

[Steel Octagon Boxes, Covers,  
Adjustable Bar Hangers and  
Ceiling Pans UL certification](#)

**SPECIFICATIONS AND  
DATASHEETS**

[Steel Outlet Boxes for  
Electrical Systems](#)

[Eaton Specification Sheet -  
TP301](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



# Specifications

## Eaton TP301

Eaton Crouse-Hinds series Ceiling Fan Box, (3) 1/2", 4", 1/2", Steel, Fan rated, fixture rated, 6.0 cubic inch capacity

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series ceiling fan box
<b>CATALOG NUMBER</b>	TP301
<b>UPC</b>	786189103014
<b>PRODUCT LENGTH/DEPTH</b>	4 in
<b>PRODUCT HEIGHT</b>	0.5 in
<b>PRODUCT WIDTH</b>	4 in
<b>PRODUCT WEIGHT</b>	0.51 lb



### Certifications and compliances

<b>AREA CLASSIFICATION</b>	Ordinary/Non-Hazardous Locations
<b>STANDARDS TYPE</b>	NEC/CEC

### Product specifications

<b>BOX SIZE</b>	4"
<b>DEPTH</b>	1/2"
<b>CAPACITY</b>	6 cubic in
<b>BOTTOM KNOCKOUTS</b>	(3) 1/2 in
<b>MATERIAL</b>	Steel
<b>SPECIAL FEATURES</b>	Fan rated, fixture rated

### Resources

<b>CATALOGS</b>	<a href="#">Crouse-Hinds series Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans catalog page</a>
-----------------	---

**CERTIFICATION  
REPORTS**

[Steel Octagon Boxes, Covers,  
Adjustable Bar Hangers and  
Ceiling Pans Canadian  
certification](#)

[Steel Octagon Boxes, Covers,  
Adjustable Bar Hangers and  
Ceiling Pans UL certification](#)

**SPECIFICATIONS AND  
DATASHEETS**

[Steel Outlet Boxes for  
Electrical Systems](#)

[Eaton Specification Sheet -  
TP301](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights  
Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest  
product and support information.

All other trademarks are property of  
their respective owners.

