

Specifications



Eaton TP414

Eaton Crouse-Hinds series Square Outlet Box, (3) 1/2", (2) 3/4", 4", Conduit (no clamps), Drawn, 1-1/2", Steel, (8) 1/2", (4) 3/4", 22.0 cubic inch capacity

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series square outlet box
CATALOG NUMBER	TP414
UPC	786189104141
PRODUCT LENGTH/DEPTH	4 in
PRODUCT HEIGHT	1.5 in
PRODUCT WIDTH	4 in
PRODUCT WEIGHT	0.67 lb



Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC

Product specifications

BOX SIZE	4"
CAPACITY	22 cubic in
DEPTH	1-1/2"
CONDUIT/CABLE	Conduit (no clamps)

CONSTRUCTION	Drawn
SIDE KNOCKOUTS	(8) 1/2 in, (4) 3/4 in
BOTTOM KNOCKOUTS	(3) 1/2 in, (2) 3/4 in
MATERIAL	Steel

Resources

CATALOGS [Crouse-Hinds series 4-Inch Steel Square Boxes and Covers catalog page](#)

CERTIFICATION REPORTS [4-Inch Steel Square Outlet Boxes, Covers, Extension Rings UL certification](#)
[4-Inch Steel Square Outlet Boxes, Covers, Extension Rings Canadian certification](#)

SPECIFICATIONS AND DATASHEETS [Steel Outlet Boxes for Electrical Systems](#)
[Eaton Specification Sheet - TP414](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications



Eaton TP414

Eaton Crouse-Hinds series Square Outlet Box, (3) 1/2", (2) 3/4", 4", Conduit (no clamps), Drawn, 1-1/2", Steel, (8) 1/2", (4) 3/4", 22.0 cubic inch capacity

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series square outlet box
CATALOG NUMBER	TP414
UPC	786189104141
PRODUCT LENGTH/DEPTH	4 in
PRODUCT HEIGHT	1.5 in
PRODUCT WIDTH	4 in
PRODUCT WEIGHT	0.67 lb



Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC

Product specifications

BOX SIZE	4"
CAPACITY	22 cubic in
DEPTH	1-1/2"
CONDUIT/CABLE	Conduit (no clamps)

CONSTRUCTION	Drawn
SIDE KNOCKOUTS	(8) 1/2 in, (4) 3/4 in
BOTTOM KNOCKOUTS	(3) 1/2 in, (2) 3/4 in
MATERIAL	Steel

Resources

CATALOGS [Crouse-Hinds series 4-Inch Steel Square Boxes and Covers catalog page](#)

CERTIFICATION REPORTS [4-Inch Steel Square Outlet Boxes, Covers, Extension Rings UL certification](#)
[4-Inch Steel Square Outlet Boxes, Covers, Extension Rings Canadian certification](#)

SPECIFICATIONS AND DATASHEETS [Steel Outlet Boxes for Electrical Systems](#)
[Eaton Specification Sheet - TP414](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
 Eaton House
 30 Pembroke Road
 Dublin 4, Ireland
 Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

