

# Specifications



## Eaton TP423

Eaton Crouse-Hinds series Square Outlet Box, (2) 1/2", (2) 1/2", (1) 3/4" E, 4", VMS, Conduit (no clamps), Welded, 1-1/2", Steel, (6) 1/2", (3) 1/2", (1) 3/4" E, 22.0 cubic inch capacity

### General specifications

PRODUCT NAME	Eaton Crouse-Hinds series square outlet box
CATALOG NUMBER	TP423
UPC	786189104233
PRODUCT LENGTH/DEPTH	4 in
PRODUCT HEIGHT	1.5 in
PRODUCT WIDTH	4 in
PRODUCT WEIGHT	0.81 lb



### Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC

### Product specifications

BOX SIZE	4"
CAPACITY	22 cubic in
DEPTH	1-1/2"
CONDUIT/CABLE	Conduit (no clamps)

<b>BRACKET STYLE</b>	VMS
<b>CONSTRUCTION</b>	Welded
<b>SIDE KNOCKOUTS</b>	(6) 1/2 in, (3) 1/2 in, (1) 3/4 in E
<b>BOTTOM KNOCKOUTS</b>	(2) 1/2 in, (2) 1/2 in, (1) 3/4 in E
<b>MATERIAL</b>	Steel

## Resources

### CATALOGS

[Crouse-Hinds series 4-Inch Steel Square Boxes and Covers catalog page](#)

### CERTIFICATION REPORTS

[4-Inch Steel Square Outlet Boxes, Covers, Extension Rings Canadian certification](#)

[4-Inch Steel Square Outlet Boxes, Covers, Extension Rings UL certification](#)

### SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - TP423](#)

[Steel Outlet Boxes for Electrical Systems](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



# Specifications



## Eaton TP423

Eaton Crouse-Hinds series Square Outlet Box, (2) 1/2", (2) 1/2", (1) 3/4" E, 4", VMS, Conduit (no clamps), Welded, 1-1/2", Steel, (6) 1/2", (3) 1/2", (1) 3/4" E, 22.0 cubic inch capacity

### General specifications

PRODUCT NAME	Eaton Crouse-Hinds series square outlet box
CATALOG NUMBER	TP423
UPC	786189104233
PRODUCT LENGTH/DEPTH	4 in
PRODUCT HEIGHT	1.5 in
PRODUCT WIDTH	4 in
PRODUCT WEIGHT	0.81 lb



### Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC

### Product specifications

BOX SIZE	4"
CAPACITY	22 cubic in
DEPTH	1-1/2"
CONDUIT/CABLE	Conduit (no clamps)

<b>BRACKET STYLE</b>	VMS
<b>CONSTRUCTION</b>	Welded
<b>SIDE KNOCKOUTS</b>	(6) 1/2 in, (3) 1/2 in, (1) 3/4 in E
<b>BOTTOM KNOCKOUTS</b>	(2) 1/2 in, (2) 1/2 in, (1) 3/4 in E
<b>MATERIAL</b>	Steel

## Resources

### CATALOGS

[Crouse-Hinds series 4-Inch  
Steel Square Boxes and Covers  
catalog page](#)

### CERTIFICATION REPORTS

[4-Inch Steel Square Outlet  
Boxes, Covers, Extension  
Rings Canadian certification](#)

[4-Inch Steel Square Outlet  
Boxes, Covers, Extension  
Rings UL certification](#)

### SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet -  
TP423](#)

[Steel Outlet Boxes for  
Electrical Systems](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights  
Reserved.

Eaton is a registered trademark.

All other trademarks are property of  
their respective owners.

Follow us on social media to get the latest  
product and support information.

