

# Eaton TP434

Catalog Number: TP434

Eaton Crouse-Hinds series Square Outlet Box, (3) 1/2", (2) 3/4", 4", Conduit (no clamps), Drawn, 2-1/8", Steel, (8) 1/2", (4) 3/4", 30.3 cubic inch capacity

## General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series square outlet box	TP434
	UPC
	786189104349
Product Length/Depth	Product Height
4 in	2.13 in
Product Width	Product Weight
4 in	1 lb



## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

## Product specifications

### Box size

4"

### Capacity

30.3 cubic in

### Depth

2-1/8"

### Conduit/cable

Conduit (no clamps)

### Construction

Drawn

### Side knockouts

(8) 1/2 in, (4) 3/4 in

### Bottom Knockouts

(3) 1/2 in, (2) 3/4 in

### Material

Steel

## Resources

### Catalogs

[Crouse-Hinds series 4-Inch Steel Square Boxes and Covers catalog page](#)

### Certification reports

[4-Inch Steel Square Outlet Boxes, Covers, Extension Rings Canadian certification](#)

[4-Inch Steel Square Outlet Boxes, Covers, Extension Rings UL certification](#)

### Specifications and datasheets

[Eaton Specification Sheet - TP434](#)

[Steel Outlet Boxes for Electrical Systems](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton TP434

Catalog Number: TP434

Eaton Crouse-Hinds series Square Outlet Box, (3) 1/2", (2) 3/4", 4", Conduit (no clamps), Drawn, 2-1/8", Steel, (8) 1/2", (4) 3/4", 30.3 cubic inch capacity

## General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series square outlet box	TP434
	UPC
	786189104349
Product Length/Depth	Product Height
4 in	2.13 in
Product Width	Product Weight
4 in	1 lb



## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

## Product specifications

### Box size

4"

### Capacity

30.3 cubic in

### Depth

2-1/8"

### Conduit/cable

Conduit (no clamps)

### Construction

Drawn

### Side knockouts

(8) 1/2 in, (4) 3/4 in

### Bottom Knockouts

(3) 1/2 in, (2) 3/4 in

### Material

Steel

## Resources

### Catalogs

[Crouse-Hinds series 4-Inch Steel Square Boxes and Covers catalog page](#)

### Certification reports

[4-Inch Steel Square Outlet Boxes, Covers, Extension Rings Canadian certification](#)

[4-Inch Steel Square Outlet Boxes, Covers, Extension Rings UL certification](#)

### Specifications and datasheets

[Eaton Specification Sheet - TP434](#)

[Steel Outlet Boxes for Electrical Systems](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)