

Eaton TP404

Catalog Number: TP404

Eaton Crouse-Hinds series Square Outlet Box, (2) 1/2", (2) 1/2", (1) 3/4" E, 4", Conduit (no clamps), Welded, 1-1/2", Steel, (8) 1/2", (4) 1/2", (1) 3/4" E, 22.0 cubic inch capacity



General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series square outlet box	TP404
	UPC
	786189104042
Product Length/Depth	Product Height
4 in	1.5 in
Product Width	Product Weight
4 in	0.72 lb

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

Product specifications

Box size

4"

Capacity

22 cubic in

Depth

1-1/2"

Conduit/cable

Conduit (no clamps)

Construction

Welded

Side knockouts

(8) 1/2 in, (4) 1/2 in, (1) 3/4 in E

Bottom Knockouts

(2) 1/2 in, (2) 1/2 in, (1) 3/4 in E

Material

Steel

Resources

Catalogs

[Crouse-Hinds series 4-Inch Steel Square Boxes and Covers catalog page](#)

Certification reports

[4-Inch Steel Square Outlet Boxes, Covers, Extension Rings UL certification](#)

[4-Inch Steel Square Outlet Boxes, Covers, Extension Rings Canadian certification](#)

Specifications and datasheets

[Steel Outlet Boxes for Electrical Systems](#)

[Eaton Specification Sheet - TP404](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton TP404

Catalog Number: TP404

Eaton Crouse-Hinds series Square Outlet Box, (2) 1/2", (2) 1/2", (1) 3/4" E, 4", Conduit (no clamps), Welded, 1-1/2", Steel, (8) 1/2", (4) 1/2", (1) 3/4" E, 22.0 cubic inch capacity



General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series square outlet box	TP404
	UPC
	786189104042
Product Length/Depth	Product Height
4 in	1.5 in
Product Width	Product Weight
4 in	0.72 lb

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

Product specifications

Box size

4"

Capacity

22 cubic in

Depth

1-1/2"

Conduit/cable

Conduit (no clamps)

Construction

Welded

Side knockouts

(8) 1/2 in, (4) 1/2 in, (1) 3/4 in E

Bottom Knockouts

(2) 1/2 in, (2) 1/2 in, (1) 3/4 in E

Material

Steel

Resources

Catalogs

[Crouse-Hinds series 4-Inch Steel Square Boxes and Covers catalog page](#)

Certification reports

[4-Inch Steel Square Outlet Boxes, Covers, Extension Rings UL certification](#)

[4-Inch Steel Square Outlet Boxes, Covers, Extension Rings Canadian certification](#)

Specifications and datasheets

[Steel Outlet Boxes for Electrical Systems](#)

[Eaton Specification Sheet - TP404](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)