

Specifications



Photo is representative

Eaton TP432PF

Eaton Crouse-Hinds series Square Outlet Box, (2) 1/2", (2) 1/2", (1) 3/4" E, 4", Conduit (no clamps), Welded, 2-1/8", Steel, (8) 3/4", Includes ground screw with pigtail lead, 30.3 cubic inch capacity

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series square outlet box
CATALOG NUMBER	TP432PF
UPC	662279000916
PRODUCT LENGTH/DEPTH	4 in
PRODUCT HEIGHT	2.13 in
PRODUCT WIDTH	4 in
PRODUCT WEIGHT	0.93 lb



Powering Business Worldwide

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC

Product specifications

BOX SIZE	4"
CAPACITY	30.3 cubic in
DEPTH	2-1/8"
CONDUIT/CABLE	Conduit (no clamps)
CONSTRUCTION	Welded
SIDE KNOCKOUTS	(8) 3/4 in
BOTTOM KNOCKOUTS	(2) 1/2 in, (2) 1/2 in, (1) 3/4 in E
MATERIAL	Steel
SPECIAL FEATURES	Includes ground screw with pigtail lead

Resources

CATALOGS	Crouse-Hinds series 4-Inch Steel Square Boxes and Covers catalog page
CERTIFICATION REPORTS	4-Inch Steel Square Outlet Boxes, Covers, Extension Rings UL certification 4-Inch Steel Square Outlet Boxes, Covers, Extension Rings Canadian certification
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - TP432PF Steel Outlet Boxes for Electrical Systems

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.

Specifications



Photo is representative

Eaton TP432PF

Eaton Crouse-Hinds series Square Outlet Box, (2) 1/2", (2) 1/2", (1) 3/4" E, 4", Conduit (no clamps), Welded, 2-1/8", Steel, (8) 3/4", Includes ground screw with pigtail lead, 30.3 cubic inch capacity

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series square outlet box
CATALOG NUMBER	TP432PF
UPC	662279000916
PRODUCT LENGTH/DEPTH	4 in
PRODUCT HEIGHT	2.13 in
PRODUCT WIDTH	4 in
PRODUCT WEIGHT	0.93 lb

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC

Product specifications

BOX SIZE	4"
CAPACITY	30.3 cubic in
DEPTH	2-1/8"
CONDUIT/CABLE	Conduit (no clamps)
CONSTRUCTION	Welded
SIDE KNOCKOUTS	(8) 3/4 in
BOTTOM KNOCKOUTS	(2) 1/2 in, (2) 1/2 in, (1) 3/4 in E
MATERIAL	Steel
SPECIAL FEATURES	Includes ground screw with pigtail lead

Resources

CATALOGS	Crouse-Hinds series 4-Inch Steel Square Boxes and Covers catalog page
CERTIFICATION REPORTS	4-Inch Steel Square Outlet Boxes, Covers, Extension Rings UL certification 4-Inch Steel Square Outlet Boxes, Covers, Extension Rings Canadian certification
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - TP432PF Steel Outlet Boxes for Electrical Systems

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.