

Eaton TP574

Catalog Number: TP574

Eaton Crouse-Hinds series Square Cover, 4-11/16", Natural, Raised surface, one device, Steel, 1/4" raised, 1.8 cubic inch capacity



General specifications

| | |
|--|----------------------|
| Product Name | Catalog Number |
| Eaton Crouse-Hinds series square cover | TP574 |
| UPC | Product Length/Depth |
| 786189105742 | 4.69 in |
| Product Height | Product Width |
| 0.25 in | 4.69 in |
| Product Weight | |
| 0.32 lb | |

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

Product specifications

Box size

4-11/16"

Capacity

1.8 cubic in

Color

Natural

Configuration

Raised surface, one device

Material

Steel

Type

1/4" raised

Resources

3D CAD drawing package

[Eaton Crouse-Hinds TP574 3D drawing](#)

Catalogs

[Crouse-Hinds series 4-11/16 Inch Steel Square Boxes and Covers catalog page](#)

Certification reports

[4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings UL certification](#)

[4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings Canadian certification](#)

Specifications and datasheets

[Eaton Specification Sheet - TP574](#)

[Steel Outlet Boxes for Electrical Systems](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton TP574

Catalog Number: TP574

Eaton Crouse-Hinds series Square Cover, 4-11/16", Natural, Raised surface, one device, Steel, 1/4" raised, 1.8 cubic inch capacity



General specifications

| | |
|--|----------------------|
| Product Name | Catalog Number |
| Eaton Crouse-Hinds series square cover | TP574 |
| UPC | Product Length/Depth |
| 786189105742 | 4.69 in |
| Product Height | Product Width |
| 0.25 in | 4.69 in |
| Product Weight | |
| 0.32 lb | |

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

Product specifications

Box size

4-11/16"

Capacity

1.8 cubic in

Color

Natural

Configuration

Raised surface, one device

Material

Steel

Type

1/4" raised

Resources

3D CAD drawing package

[Eaton Crouse-Hinds TP574 3D drawing](#)

Catalogs

[Crouse-Hinds series 4-11/16 Inch Steel Square Boxes and Covers catalog page](#)

Certification reports

[4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings UL certification](#)

[4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings Canadian certification](#)

Specifications and datasheets

[Eaton Specification Sheet - TP574](#)

[Steel Outlet Boxes for Electrical Systems](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)