

Specifications



Photo is representative

Eaton TP578

Eaton Crouse-Hinds series Square Cover, 4-11/16", Natural, Raised surface, one device, Steel, 3/4" raised, 5.0 cubic inch capacity

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series square cover
CATALOG NUMBER	TP578
UPC	786189105780
PRODUCT LENGTH/DEPTH	4.69 in
PRODUCT HEIGHT	0.75 in
PRODUCT WIDTH	4.69 in
PRODUCT WEIGHT	0.42 lb



Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous
---------------------	------------------------

Product specifications

BOX SIZE	4-11/16"
----------	----------

	Locations
STANDARDS TYPE	NEC/CEC

CAPACITY	5 cubic in
COLOR	Natural
CONFIGURATION	Raised surface, one device
MATERIAL	Steel
TYPE	3/4" raised

Resources

3D CAD DRAWING PACKAGE [Eaton Crouse-Hinds TP578 3D drawing](#)

CATALOGS [Crouse-Hinds series 4-11/16 Inch Steel Square Boxes and Covers catalog page](#)

CERTIFICATION REPORTS [4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings UL certification](#)

CERTIFICATION REPORTS [4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings Canadian certification](#)

SPECIFICATIONS AND DATASHEETS [Steel Outlet Boxes for Electrical Systems](#)
[Eaton Specification Sheet - TP578](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

Reserved.



Specifications



Photo is representative

Eaton TP578

Eaton Crouse-Hinds series Square Cover, 4-11/16", Natural, Raised surface, one device, Steel, 3/4" raised, 5.0 cubic inch capacity

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series square cover
CATALOG NUMBER	TP578
UPC	786189105780
PRODUCT LENGTH/DEPTH	4.69 in
PRODUCT HEIGHT	0.75 in
PRODUCT WIDTH	4.69 in
PRODUCT WEIGHT	0.42 lb



Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous
---------------------	------------------------

Product specifications

BOX SIZE	4-11/16"
----------	----------

	Locations
STANDARDS TYPE	NEC/CEC

CAPACITY	5 cubic in
COLOR	Natural
CONFIGURATION	Raised surface, one device
MATERIAL	Steel
TYPE	3/4" raised

Resources

3D CAD DRAWING PACKAGE [Eaton Crouse-Hinds TP578 3D drawing](#)

CATALOGS [Crouse-Hinds series 4-11/16 Inch Steel Square Boxes and Covers catalog page](#)

CERTIFICATION REPORTS [4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings UL certification](#)

CERTIFICATION REPORTS [4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings Canadian certification](#)

SPECIFICATIONS AND DATASHEETS [Steel Outlet Boxes for Electrical Systems](#)
[Eaton Specification Sheet - TP578](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

Reserved.

