

Eaton TP675

Catalog Number: TP675

Eaton Crouse-Hinds series Masonry Box, (2) 1/2", (2) 3/4", 3-1/2", (2) 1/2", (2) 3/4", Steel, Single-gang, (4) 1/2", (4) 3/4", Gangable, 22.0 cubic inch capacity



General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series masonry box	TP675
UPC	Product Length/Depth
786189106756	3.75 in
Product Height	Product Width
3.75 in	1.94 in
Product Weight	
0.82 lb	

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

Product specifications

Depth

3-1/2"

Number of gangs

Single-gang

End Knockouts

(2) 1/2 in, (2) 3/4 in

Side knockouts

(4) 1/2 in, (4) 3/4 in

Bottom Knockouts

(2) 1/2 in, (2) 3/4 in

Capacity

22 cubic in

Material

Steel

Type

Gangable

Resources

Catalogs

[Crouse-Hinds series Steel Masonry Boxes catalog page](#)

Certification reports

[Steel Masonry Boxes Canadian certification](#)

[Steel Masonry Boxes UL certification](#)

Specifications and datasheets

[Eaton Specification Sheet - TP675](#)

[Steel Outlet Boxes for Electrical Systems](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton TP675

Catalog Number: TP675

Eaton Crouse-Hinds series Masonry Box, (2) 1/2", (2) 3/4", 3-1/2", (2) 1/2", (2) 3/4", Steel, Single-gang, (4) 1/2", (4) 3/4", Gangable, 22.0 cubic inch capacity



General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series masonry box	TP675
UPC	Product Length/Depth
786189106756	3.75 in
Product Height	Product Width
3.75 in	1.94 in
Product Weight	
0.82 lb	

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

Product specifications

Depth

3-1/2"

Number of gangs

Single-gang

End Knockouts

(2) 1/2 in, (2) 3/4 in

Side knockouts

(4) 1/2 in, (4) 3/4 in

Bottom Knockouts

(2) 1/2 in, (2) 3/4 in

Capacity

22 cubic in

Material

Steel

Type

Gangable

Resources

Catalogs

[Crouse-Hinds series Steel Masonry Boxes catalog page](#)

Certification reports

[Steel Masonry Boxes Canadian certification](#)

[Steel Masonry Boxes UL certification](#)

Specifications and datasheets

[Eaton Specification Sheet - TP675](#)

[Steel Outlet Boxes for Electrical Systems](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)