



# Specifications



## Eaton TP684

Eaton Crouse-Hinds series Masonry Box, (6) 1/2", (6) 3/4", 2-1/2", (3) 1/2", (3) 3/4", Steel, Three-gang, (2) 1/2", (2) 3/4", 46.5 cubic inch capacity

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series masonry box
<b>CATALOG NUMBER</b>	TP684
<b>UPC</b>	786189106848
<b>PRODUCT LENGTH/DEPTH</b>	5.56 in
<b>PRODUCT HEIGHT</b>	3.75 in
<b>PRODUCT WIDTH</b>	3.75 in
<b>PRODUCT WEIGHT</b>	1.29 lb



Powering Business Worldwide

## Certifications and compliances

<b>AREA CLASSIFICATION</b>	Ordinary/Non-Hazardous Locations
<b>STANDARDS TYPE</b>	NEC/CEC

## Product specifications

<b>DEPTH</b>	2-1/2"
<b>NUMBER OF GANGS</b>	Three-gang
<b>END KNOCKOUTS</b>	(3) 1/2 in, (3) 3/4 in
<b>SIDE KNOCKOUTS</b>	(2) 1/2 in, (2) 3/4 in
<b>BOTTOM KNOCKOUTS</b>	(6) 1/2 in, (6) 3/4 in
<b>CAPACITY</b>	46.5 cubic in
<b>MATERIAL</b>	Steel

## Resources

CATALOGS	<a href="#">Crouse-Hinds series Steel Masonry Boxes catalog page</a>
----------	--

CERTIFICATION REPORTS	<a href="#">Steel Masonry Boxes UL certification</a> <a href="#">Steel Masonry Boxes Canadian certification</a>
-----------------------	--

SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - TP684</a> <a href="#">Steel Outlet Boxes for Electrical Systems</a>
-------------------------------	--

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**





**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.

# Specifications



## Eaton TP684

Eaton Crouse-Hinds series Masonry Box, (6) 1/2", (6) 3/4", 2-1/2", (3) 1/2", (3) 3/4", Steel, Three-gang, (2) 1/2", (2) 3/4", 46.5 cubic inch capacity

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series masonry box
<b>CATALOG NUMBER</b>	TP684
<b>UPC</b>	786189106848
<b>PRODUCT LENGTH/DEPTH</b>	5.56 in
<b>PRODUCT HEIGHT</b>	3.75 in
<b>PRODUCT WIDTH</b>	3.75 in
<b>PRODUCT WEIGHT</b>	1.29 lb



Powering Business Worldwide

## Certifications and compliances

<b>AREA CLASSIFICATION</b>	Ordinary/Non-Hazardous Locations
<b>STANDARDS TYPE</b>	NEC/CEC

## Product specifications

<b>DEPTH</b>	2-1/2"
<b>NUMBER OF GANGS</b>	Three-gang
<b>END KNOCKOUTS</b>	(3) 1/2 in, (3) 3/4 in
<b>SIDE KNOCKOUTS</b>	(2) 1/2 in, (2) 3/4 in
<b>BOTTOM KNOCKOUTS</b>	(6) 1/2 in, (6) 3/4 in
<b>CAPACITY</b>	46.5 cubic in
<b>MATERIAL</b>	Steel

## Resources

CATALOGS	<a href="#">Crouse-Hinds series Steel Masonry Boxes catalog page</a>
----------	--

CERTIFICATION REPORTS	<a href="#">Steel Masonry Boxes UL certification</a> <a href="#">Steel Masonry Boxes Canadian certification</a>
-----------------------	--

SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - TP684</a> <a href="#">Steel Outlet Boxes for Electrical Systems</a>
-------------------------------	--

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.