

Specifications



Photo is representative

Eaton TP692

Eaton Crouse-Hinds series Masonry Box, (6) 1/2", (6) 3/4", 3-1/2", (6) 1/2", (6) 3/4", Steel, Three-gang, (2) 1/2", (2) 3/4", 66.5 cubic inch capacity

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series masonry box
CATALOG NUMBER	TP692
UPC	786189106923
PRODUCT LENGTH/DEPTH	5.56 in
PRODUCT HEIGHT	3.75 in
PRODUCT WIDTH	3.75 in
PRODUCT WEIGHT	1.55 lb



Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous
----------------------------	------------------------

Product specifications

DEPTH	3-1/2"
--------------	--------

	Locations
STANDARDS TYPE	NEC/CEC

NUMBER OF GANGS	Three-gang
END KNOCKOUTS	(6) 1/2 in, (6) 3/4 in
SIDE KNOCKOUTS	(2) 1/2 in, (2) 3/4 in
BOTTOM KNOCKOUTS	(6) 1/2 in, (6) 3/4 in
CAPACITY	66.5 cubic in
MATERIAL	Steel

Resources

CATALOGS	Crouse-Hinds series Steel Masonry Boxes catalog page
CERTIFICATION REPORTS	Steel Masonry Boxes Canadian certification Steel Masonry Boxes UL certification
SPECIFICATIONS AND DATASHEETS	Steel Outlet Boxes for Electrical Systems Eaton Specification Sheet - TP692

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications



Photo is representative

Eaton TP692

Eaton Crouse-Hinds series Masonry Box, (6) 1/2", (6) 3/4", 3-1/2", (6) 1/2", (6) 3/4", Steel, Three-gang, (2) 1/2", (2) 3/4", 66.5 cubic inch capacity

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series masonry box
CATALOG NUMBER	TP692
UPC	786189106923
PRODUCT LENGTH/DEPTH	5.56 in
PRODUCT HEIGHT	3.75 in
PRODUCT WIDTH	3.75 in
PRODUCT WEIGHT	1.55 lb



Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous
----------------------------	------------------------

Product specifications

DEPTH	3-1/2"
--------------	--------

	Locations
STANDARDS TYPE	NEC/CEC

NUMBER OF GANGS	Three-gang
END KNOCKOUTS	(6) 1/2 in, (6) 3/4 in
SIDE KNOCKOUTS	(2) 1/2 in, (2) 3/4 in
BOTTOM KNOCKOUTS	(6) 1/2 in, (6) 3/4 in
CAPACITY	66.5 cubic in
MATERIAL	Steel

Resources

CATALOGS	Crouse-Hinds series Steel Masonry Boxes catalog page
CERTIFICATION REPORTS	Steel Masonry Boxes Canadian certification Steel Masonry Boxes UL certification
SPECIFICATIONS AND DATASHEETS	Steel Outlet Boxes for Electrical Systems Eaton Specification Sheet - TP692

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

