

# Specifications



## Eaton TP724

Eaton Crouse-Hinds series Square Surface Cover, 4-11/16", Raised surface, Steel, For one single receptacle 1-13/32" diameter, 9.0 cubic inch capacity

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series square surface cover
<b>CATALOG NUMBER</b>	TP724
<b>UPC</b>	786189107241
<b>PRODUCT LENGTH/DEPTH</b>	4.69 in
<b>PRODUCT HEIGHT</b>	0.06 in
<b>PRODUCT WIDTH</b>	4.69 in
<b>PRODUCT WEIGHT</b>	0.53 lb



Powering Business Worldwide

### Certifications and compliances

<b>AREA CLASSIFICATION</b>	Ordinary/Non-Hazardous Locations
<b>STANDARDS TYPE</b>	NEC/CEC

### Product specifications

<b>BOX SIZE</b>	4-11/16"
<b>CAPACITY</b>	9 cubic in
<b>CONFIGURATION</b>	Raised surface
<b>MATERIAL</b>	Steel

---

**TYPE**

---

For one single receptacle 1-13/32" diameter

---

**Resources****3D CAD DRAWING PACKAGE**[Eaton Crouse-Hinds TP724 3D drawing](#)**CATALOGS**[Crouse-Hinds series 4-11/16 Inch Steel Square Boxes and Covers catalog page](#)**CERTIFICATION REPORTS**[4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings Canadian certification](#)[4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings UL certification](#)**SPECIFICATIONS AND DATASHEETS**[Eaton Specification Sheet - TP724](#)[Steel Outlet Boxes for Electrical Systems](#)

---

**PROJECT NAME:**

---

**PROJECT NUMBER:**

---

**PREPARED BY:**

---

**DATE:**

---



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



# Specifications



## Eaton TP724

Eaton Crouse-Hinds series Square Surface Cover, 4-11/16", Raised surface, Steel, For one single receptacle 1-13/32" diameter, 9.0 cubic inch capacity

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series square surface cover
<b>CATALOG NUMBER</b>	TP724
<b>UPC</b>	786189107241
<b>PRODUCT LENGTH/DEPTH</b>	4.69 in
<b>PRODUCT HEIGHT</b>	0.06 in
<b>PRODUCT WIDTH</b>	4.69 in
<b>PRODUCT WEIGHT</b>	0.53 lb



### Certifications and compliances

<b>AREA CLASSIFICATION</b>	Ordinary/Non-Hazardous Locations
<b>STANDARDS TYPE</b>	NEC/CEC

### Product specifications

<b>BOX SIZE</b>	4-11/16"
<b>CAPACITY</b>	9 cubic in
<b>CONFIGURATION</b>	Raised surface
<b>MATERIAL</b>	Steel

---

**TYPE**

---

For one single receptacle 1-13/32" diameter

---

**Resources****3D CAD DRAWING PACKAGE**[Eaton Crouse-Hinds TP724 3D drawing](#)**CATALOGS**[Crouse-Hinds series 4-11/16 Inch Steel Square Boxes and Covers catalog page](#)**CERTIFICATION REPORTS**[4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings Canadian certification](#)[4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings UL certification](#)**SPECIFICATIONS AND DATASHEETS**[Eaton Specification Sheet - TP724](#)[Steel Outlet Boxes for Electrical Systems](#)

---

**PROJECT NAME:**

---

**PROJECT NUMBER:**

---

**PREPARED BY:**

---

**DATE:**

---



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

