

Specifications



Photo is representative

Eaton TP678

Eaton Crouse-Hinds series Switch Box, (1) 1/2", Conduit (no clamps), 2-3/4", (1) 3/4", Steel, (1) 3/4", Ears, Gangable, 14.0 cubic inch capacity

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series switch box
CATALOG NUMBER	TP678
UPC	786189106787
PRODUCT LENGTH/DEPTH	2 in
PRODUCT HEIGHT	3 in
PRODUCT WIDTH	2.75 in
PRODUCT WEIGHT	0.61 lb

EATON

Powering Business Worldwide

Certifications and compliances

AREA CLASSIFICATION Ordinary/Non-Hazardous

Product specifications

DEPTH 2-3/4"

	Locations
STANDARDS TYPE	NEC/CEC

TYPE	Gangable
CAPACITY	14 cubic in
CONDUIT/CABLE	Conduit (no clamps)
END KNOCKOUTS	(1) 3/4 in
SIDE KNOCKOUTS	(1) 3/4 in
BOTTOM KNOCKOUTS	(1) 1/2 in
MATERIAL	Steel
SPECIAL FEATURES	Ears

Resources

CATALOGS	Crouse-Hinds series Steel Switch Boxes catalog page
CERTIFICATION REPORTS	Steel Switch Boxes Canadian certification Steel Switch Boxes UL certification
SPECIFICATIONS AND DATASHEETS	Steel Outlet Boxes for Electrical Systems Eaton Specification Sheet - TP678

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications



Photo is representative

Eaton TP678

Eaton Crouse-Hinds series Switch Box, (1) 1/2", Conduit (no clamps), 2-3/4", (1) 3/4", Steel, (1) 3/4", Ears, Gangable, 14.0 cubic inch capacity

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series switch box
CATALOG NUMBER	TP678
UPC	786189106787
PRODUCT LENGTH/DEPTH	2 in
PRODUCT HEIGHT	3 in
PRODUCT WIDTH	2.75 in
PRODUCT WEIGHT	0.61 lb



Certifications and compliances

AREA CLASSIFICATION Ordinary/Non-Hazardous

Product specifications

DEPTH 2-3/4"

	Locations
STANDARDS TYPE	NEC/CEC

TYPE	Gangable
CAPACITY	14 cubic in
CONDUIT/CABLE	Conduit (no clamps)
END KNOCKOUTS	(1) 3/4 in
SIDE KNOCKOUTS	(1) 3/4 in
BOTTOM KNOCKOUTS	(1) 1/2 in
MATERIAL	Steel
SPECIAL FEATURES	Ears

Resources

CATALOGS	Crouse-Hinds series Steel Switch Boxes catalog page
CERTIFICATION REPORTS	Steel Switch Boxes Canadian certification Steel Switch Boxes UL certification
SPECIFICATIONS AND DATASHEETS	Steel Outlet Boxes for Electrical Systems Eaton Specification Sheet - TP678

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

