


# Specifications



## Eaton TP685

Eaton Crouse-Hinds series Masonry Box, (8) 1/2", (8) 3/4", 2-1/2", (4) 1/2", (4) 3/4", Steel, Four-gang, (2) 1/2", (2) 3/4", 62.0 cubic inch capacity

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series masonry box
<b>CATALOG NUMBER</b>	TP685
<b>UPC</b>	786189106855
<b>PRODUCT LENGTH/DEPTH</b>	7.38 in
<b>PRODUCT HEIGHT</b>	3.75 in
<b>PRODUCT WIDTH</b>	3.75 in
<b>PRODUCT WEIGHT</b>	1.65 lb



Powering Business Worldwide

## Certifications and compliances

<b>AREA CLASSIFICATION</b>	Ordinary/Non-Hazardous Locations
<b>STANDARDS TYPE</b>	NEC/CEC

## Product specifications

<b>DEPTH</b>	2-1/2"
<b>NUMBER OF GANGS</b>	Four-gang
<b>END KNOCKOUTS</b>	(4) 1/2 in, (4) 3/4 in
<b>SIDE KNOCKOUTS</b>	(2) 1/2 in, (2) 3/4 in
<b>BOTTOM KNOCKOUTS</b>	(8) 1/2 in, (8) 3/4 in
<b>CAPACITY</b>	62 cubic in
<b>MATERIAL</b>	Steel

## Resources

CATALOGS	<a href="#">Crouse-Hinds series Steel Masonry Boxes catalog page</a>
----------	--

CERTIFICATION REPORTS	<a href="#">Steel Masonry Boxes UL certification</a> <a href="#">Steel Masonry Boxes Canadian certification</a>
-----------------------	--

SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - TP685</a> <a href="#">Steel Outlet Boxes for Electrical Systems</a>
-------------------------------	--

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**




**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.

# Specifications



## Eaton TP685

Eaton Crouse-Hinds series Masonry Box, (8) 1/2", (8) 3/4", 2-1/2", (4) 1/2", (4) 3/4", Steel, Four-gang, (2) 1/2", (2) 3/4", 62.0 cubic inch capacity

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series masonry box
<b>CATALOG NUMBER</b>	TP685
<b>UPC</b>	786189106855
<b>PRODUCT LENGTH/DEPTH</b>	7.38 in
<b>PRODUCT HEIGHT</b>	3.75 in
<b>PRODUCT WIDTH</b>	3.75 in
<b>PRODUCT WEIGHT</b>	1.65 lb



Powering Business Worldwide

## Certifications and compliances

<b>AREA CLASSIFICATION</b>	Ordinary/Non-Hazardous Locations
<b>STANDARDS TYPE</b>	NEC/CEC

## Product specifications

<b>DEPTH</b>	2-1/2"
<b>NUMBER OF GANGS</b>	Four-gang
<b>END KNOCKOUTS</b>	(4) 1/2 in, (4) 3/4 in
<b>SIDE KNOCKOUTS</b>	(2) 1/2 in, (2) 3/4 in
<b>BOTTOM KNOCKOUTS</b>	(8) 1/2 in, (8) 3/4 in
<b>CAPACITY</b>	62 cubic in
<b>MATERIAL</b>	Steel

## Resources

CATALOGS	<a href="#">Crouse-Hinds series Steel Masonry Boxes catalog page</a>
----------	--

CERTIFICATION REPORTS	<a href="#">Steel Masonry Boxes UL certification</a> <a href="#">Steel Masonry Boxes Canadian certification</a>
-----------------------	--

SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - TP685</a> <a href="#">Steel Outlet Boxes for Electrical Systems</a>
-------------------------------	--

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.