
TOGGLE SWITCH OPENINGS, SIX GANG, WHITE

TP6W | [Pass & Seymour](#)

FEATURES & BENEFITS

Trademaster Plate 6gang 6toggle White



- Molded of rugged, practically indestructible self-extinguishing nylon. ("TP" series only.)
- Available in "TP" series, extra 3/16 inch width and height than Standard size plates; and "TPJ" series, extra 3/16 inch width and height than Junior-Jumbo size plates.
- Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond.
- Preferred for hospital, industrial, institutional, and other high-abuse applications.
- Nominal thickness, .070 inch.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: White
Size: Standard
Type: Toggle

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: No
CUL Listing No: No
cULus: Yes
cURus: No
Federal Spec: No
UL Listing No: No
UN SPSC: 39121704
UR: No

DIMENSIONS

Depth (US): 12.5

Width (US): 5

Volume: 18.75

Weight: 0.23765

Height: 0.3

TECHNICAL INFORMATION

Material: Plastic

Capacity: 6-gang

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA

Buy American Act Status: Buy American Act Compliant



TOGGLE SWITCH OPENINGS, SIX GANG, WHITE

TP6W | [Pass & Seymour](#)

FEATURES & BENEFITS

Trademaster Plate 6gang 6toggle White



- Molded of rugged, practically indestructible self-extinguishing nylon. ("TP" series only.)
- Available in "TP" series, extra 3/16 inch width and height than Standard size plates; and "TPJ" series, extra 3/16 inch width and height than Junior-Jumbo size plates.
- Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond.
- Preferred for hospital, industrial, institutional, and other high-abuse applications.
- Nominal thickness, .070 inch.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: White
Size: Standard
Type: Toggle

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: No
CUL Listing No: No
cULus: Yes
cURus: No
Federal Spec: No
UL Listing No: No
UN SPSC: 39121704
UR: No

DIMENSIONS

Depth (US): 12.5

Width (US): 5

Volume: 18.75

Weight: 0.23765

Height: 0.3

TECHNICAL INFORMATION

Material: Plastic

Capacity: 6-gang

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA

Buy American Act Status: Buy American Act Compliant

