



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## TR5262USBGRY Duplex Recp 15A TR Spec W/3.1A Usb Charge Gy

*Pass & Seymour/Legrand*

Catalog Number	TR5262USBGRY
Manufacturer	Pass & Seymour/Legrand
Description	Designed For Commercial Markets With Strength and Durability In Mind, This Combination Duplex Receptacle and Two Usb Type-A Features 3.1A Overall Usb Charging Capability and Is Compatible With Usb 2.0 & 3.0 Devices. For Detailed Tamper-Resistant Receptacle Information, Visit Our Tamper-Resistant Receptacles Page.
Weight per unit	0.3392 (lbs/each)
Product Category	Combination Devices

### Features

amperage rating	15
connection	Side & Back Wired
Dielectric Strength	Withstands 2000V minimum
indoor/outdoor	Indoor
Number of Wires	3
Outlet Type	Tamper-Resistant, USB-Charging
Phase	1
Poles	2
Voltage	125.0 V
Voltage Rating	125
Wall Plate Included	NO
Wire Size	14 - 10

### Material, Color, and Finish

Finish	Matte
--------	-------

### Dimensions and Weight

Depth	1.392
Height	3.281
Width	1.693



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	DUPLEX RECP 15A TR SPEC W/3.1A USB CHARGE GY
extra long description	P&S TR5262USBGRY DUP REC 15A TR SPE
Features	Single Piece Plated Steel Mounting Strap, USB-A Charging
Long Description	Designed for commercial markets with strength and durability in mind, this combination duplex receptacle and two USB Type-A features 3.1A overall USB charging capability and is compatible with USB 2.0 & 3.0 devices. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.
Product Type	Dup Rec 15A TR Spec W/3.1A Usb CHR GY
Special Features	Designed for commercial markets with strength and durability in mind, this combination USB charger duplex receptacle features 3.1A overall USB charging capability and is compatible with USB 2.0 & 3.0 devices.

## Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007031638
Manufacturers Part Number	TR-5262USBGRY
UPC	785007031638

## Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	Outlet

## Trade Size

Amperage	15.0
----------	------

## Packaging

Carton	1
Package	50
Weight Per each	0.3392

## Uses, Certifications, and Standards

Application	Commercial
environmental conditions	UL94 V2
Mounting	BOX
nema rating	5-15R
standard	UL, FEDSPEC, CULUS, CSA Listed, cULus, FSUL, UL Listed, RoHS, FEDSPEC