



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TR5362RED Duplex Recp TR B+S Wire 20A/125V RD

Pass & Seymour/LeGrand

| | |
|------------------|--|
| Catalog Number | TR5362RED |
| Manufacturer | Pass & Seymour/LeGrand |
| Description | Tamper-Resistant Hard Use Spec Grade Receptacle, Back and Side Wire, 20A, 125V |
| Weight per unit | 0.2182 (lbs/each) |
| Product Category | Gen Purpose Recept & Surge Pro |

Features

| | |
|---------------------|--|
| amperage rating | 20 |
| connection | Back and side wire |
| Dielectric Strength | Withstands 2000V minimum |
| indoor/outdoor | Indoor |
| Material | Nylon |
| media | Yes |
| Number of Wires | 3 |
| Outlet Type | Tamper-Resistant, Indoor, Commercial |
| Poles | Double Pole |
| Voltage | 125.0 V |
| Voltage Rating | 125 |
| Wattage | Electrical power is expressed in Amps and Volts. |
| Wire Size | 14 - 10 |

Material, Color, and Finish

| | |
|--------|-------|
| Color | Red |
| Finish | Matte |

Dimensions and Weight

| | |
|--------|-------|
| Height | 3.281 |
| Width | 1.130 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Description | DUPLEX RECP TR B+S WIRE 20A/125V RD |
| extra long description | P&S TR5362RED RECEP DUP TR B+S WIRE |
| Long Description | Tamper-Resistant Hard Use Spec Grade Receptacle, Back and Side Wire, 20A, 125V |
| Product Type | Recep Dup TR B+S Wire 20A/125V Red |
| Special Features | Dual mechanical shutter system to help prevent insertion of foreign objects. Auto-ground clip assures positive ground. Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring. Backed-out tri-drive brass terminal screws for faster installation. Internal screw-pressure-plate back and side wire capability. Two back wire holes for additional wiring flexibility. Corrosion-resistant plated steel strap is locked in to face and back body to resist pulling away from the face/bod |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Pass & Seymour |
| GTIN | 00785007243734 |
| Manufacturers Part Number | TR5362-RED |
| UPC | 785007243734 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|----------------------|
| Category Description | Residential Switches |
| Type | Outlet |

Trade Size

| | |
|----------|------|
| Amperage | 20.0 |
|----------|------|

Packaging

| | |
|-----------------|--------|
| Carton | 1 |
| Package | 100 |
| Weight Per each | 0.2182 |

Uses, Certifications, and Standards

| | |
|--------------------------|--------------------------------|
| Application | Commercial |
| environmental conditions | Flammability: UL94 V2 |
| Mounting | WALL |
| nema rating | 5-20R |
| standard | CULUS, UL498, CSA C22.2 No. 42 |
| Temperature Rating | -40° - 60° C |