



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TRSGFH20W Gfci TR HG Self Test Duplex 20A 125V WH

Eaton Wiring Devices

| | |
|------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number | TRSGFH20W |
| Manufacturer | Eaton Wiring Devices |
| Description | Eaton Hospital Grade Gfci Receptacle, Tamper Resistant, Self-Test, #14 - 10 Awg, 20A, Residential, Commercial, Flush, 125 V, Gfci, Back and Side Wire, White, Brass, Receptacle, Tamper Resistant, Nylon, 5-20R, Two-Pole, Three-Wire, Grounding |
| Weight per unit | 0.4050 (lbs/each) |
| Product Category | Gen Purpose Recept & Surge Pro |

Features

| | |
|-----------------|-----------------------------------|
| amperage rating | 20A |
| dimensions | 2.8130 IN X 2.0000 IN X 4.6250 IN |
| media | Yes |
| Voltage Rating | 125V |

Descriptions

| | |
|------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Description | GFCI TR HG SELF TEST DUPLEX 20A 125V WH |
| extra long description | EWD TRSGFH20W GFCI TR HG Self Test |
| Features | Tested to the highest standards to provide dependable, state-of-the-art protection suitable for residential, commercial, and industrial settings, Eaton's Ground Fault Circuit Interrupter (GFCI) receptacles are designed to recognize a ground fault in your wiring and immediately break the flow of electricity, thus protecting you from electrical shock. Additionally, they prevent resetting if, once tripped, the ground fault renders the device no longer functional. When combined with Eaton's Arc Fault Circuit I |
| Long Description | Eaton hospital grade GFCI receptacle, Tamper resistant, Self-test, #14 - 10 AWG, 20A, Residential, Commercial, Flush, 125 V, GFCI, Back and side wire, White, Brass, Receptacle, Tamper resistant, Nylon, 5-20R, Two-pole, three-wire, grounding |
| Product Type | Gfci TR HG Self Test Duplex 20A 125V WH |
| Special Features | Hospital grade GFCI |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Eaton |
| GTIN | 00032664740121 |
| Manufacturers Part Number | TRSGFH20W |
| UPC | 032664740121 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------------------|
| Category Description | Industrial GFCI devices |
| Type | Hospital grade GFCI receptacle |

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Package | 10 |
| Weight Per each | 0.405 |

Uses, Certifications, and Standards

| | |
|--------------------------|---------------------------------------------------------------------------------------------------------------|
| Application | Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other |
| environmental conditions | Tamper resistant |
| standard | NOM,cULus Listed |