

## Specification Sheet

Part Number: TSRFW-JB2



Rubber based foam tape adhesive with high ultimate bond strength conforms to any surface.

Single Gang Junction Box, 2" Deep, PVC, Office White, 1/bg

Article Number	250-10002
----------------	-----------

Type	TSR-JB2
------	---------

Color	Office White (OEWH)
-------	---------------------

Quantity Per	pack
--------------	------

Product Description	Offered in dual or single gang format, HellermannTyton's Low Voltage Junction Boxes are versatile enough for any network cabling application. Available in varying depths, these boxes are all equipped with concentric knockouts on all four sides for every TSR size of raceway to eliminate routing and installation inconvenience. all junction boxes come with adhesive strips on the back of the base and #6 screws to secure the box to the base.
---------------------	--

Short Description	Single Gang Junction Box, 2" Deep, PVC, Office White, 1/bg
-------------------	--

Global Part Name	TSR-JB2-PVC-WH
Length L (Imperial)	4.75
Length L (Metric)	120.65
Width W (Imperial)	3.0
Width W (Metric)	76.2
Height H (Imperial)	2.0
Height H (Metric)	50.80
Material	Polyvinylchloride (PVC)
Material Shortcut	PVC
Flammability	UL 94 V-0
Halogen Free	No
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	+122°F (+50°C)
Reach Compliant (Article 33)	No

ROHS Compliant	Yes
Package Quantity (Imperial)	1
Package Quantity (Metric)	1
Customs Number	3925900000

7930 N. Faulkner Road, Milwaukee, WI 53224  
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.  
[Contact Us](#)   [RoHS/WEEE Compliance](#)   [Disclaimer](#)   [Terms and Conditions](#)

## Specification Sheet

Part Number: TSRFW-JB2



Rubber based foam tape adhesive with high ultimate bond strength conforms to any surface.

Single Gang Junction Box, 2" Deep, PVC, Office White, 1/bg

Article Number	250-10002
----------------	-----------

Type	TSR-JB2
------	---------

Color	Office White (OEWH)
-------	---------------------

Quantity Per	pack
--------------	------

Product Description	Offered in dual or single gang format, HellermannTyton's Low Voltage Junction Boxes are versatile enough for any network cabling application. Available in varying depths, these boxes are all equipped with concentric knockouts on all four sides for every TSR size of raceway to eliminate routing and installation inconvenience. all junction boxes come with adhesive strips on the back of the base and #6 screws to secure the box to the base.
---------------------	--

Short Description	Single Gang Junction Box, 2" Deep, PVC, Office White, 1/bg
-------------------	--

Global Part Name	TSR-JB2-PVC-WH
Length L (Imperial)	4.75
Length L (Metric)	120.65
Width W (Imperial)	3.0
Width W (Metric)	76.2
Height H (Imperial)	2.0
Height H (Metric)	50.80
Material	Polyvinylchloride (PVC)
Material Shortcut	PVC
Flammability	UL 94 V-0
Halogen Free	No
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	+122°F (+50°C)
Reach Compliant (Article 33)	No

ROHS Compliant	Yes
Package Quantity (Imperial)	1
Package Quantity (Metric)	1
Customs Number	3925900000

7930 N. Faulkner Road, Milwaukee, WI 53224  
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.  
[Contact Us](#)   [RoHS/WEEE Compliance](#)   [Disclaimer](#)   [Terms and Conditions](#)