



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TYD50R 50FT Strap On Reel

Abb Installation Products, Inc

Catalog Number	TYD50R
Manufacturer	Abb Installation Products, Inc
Description	Deltec Cable Tie Without Double-Locking Head, Black Acetal For Temperatures Up to 85 Degrees Celsius (185 F), Weather and Ultraviolet Resistant, Length Of 15.24M (50 Foot) Reel, Width Of 12.7MM (0.5 Inch), Thickness Of 1.52MM (0.06 Inch), Tensile Strength Rating Of 1112 Newtons (250 Pounds), Can Be Cut to Any Desired Length
Weight per unit	0.9700 (lbs/each)
Product Category	Cable Ties & Wraps

Features

Tensile Strength	250
------------------	-----

Dimensions and Weight

Length	600
Thickness	0.06
Width	0.5

Descriptions

Description	50FT STRAP ON REEL
extra long description	ABB TYD-50R CABLE TIE 15X0.5IN BLK
Long Description	Deltec Cable Tie Without Double-Locking Head, Black Acetal for Temperatures up to 85 Degrees Celsius (185 F), Weather and Ultraviolet Resistant, Length of 15.24m (50 Foot) Reel, Width of 12.7mm (0.5 Inch), Thickness of 1.52mm (0.06 Inch), Tensile Strength Rating of 1112 Newtons (250 Pounds), Can Be Cut to Any Desired Length
Product Type	Cable Tie 15X0.5IN BLK Acetal 250LB
Special Features	Perfect for coaxial, fiber optic and all other communication and electrical conducting cables

Manufacturer Information

Brand	Deltec
GTIN	00786210713403
Manufacturers Part Number	TYD-50R
UPC	786210713403

Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	Strap on a Reel



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	5
Weight Per reel	0.97

Uses, Certifications, and Standards

Application	Ideal solution for bundling in harsh outdoor environments
-------------	---