

ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr. 75964-0000, TX Nacogdoches Phone: 936-569-7941 Fax: 936-560-4685



Category Description

Type

U150 5/16"-18 X 1-1/2" U-Bolt W/ Strap & Hex Nuts *L.H. Dottie CO.*

T	
Catalog Number	U150
Manufacturer	L.H. Dottie CO.
Description	U-Bolt, Low Carbon Steel Material, Zinc Plated Finish, 2-11/16 In. Length, 2 X 2-11/16 In. Size, Internal-2 In. Diameter, NC Rolled Machine Thread, 2 Nuts, Hex Nut Type, 1-1/8 In. Thread Length, 2-11/16 In. Height, 1-1/2 In. Pipe Diameter, 5/16 In. Thread Diameter
Weight per unit	0.1940 (lbs/each)
Product Category	Channel & Strut Fittings
Features	-
Thread Length	1-1/8
Material, Color, and Finish	
Finish	Zinc Plated
Dimensions and Weight	
Diameter Diameter	Internal:2
Height	2-11/16
Length	2-11/16
Size	2 x 2-11/16
Descriptions	
Description	5/16"-18 X 1-1/2" U-BOLT W/ STRAP & HEX NUTS
extra long description	DOTTIE U150 1-1/2" U-Bolts Zinc Pla
Long Description	U-Bolt, Low Carbon Steel material, Zinc Plated Finish, 2-11/16 in. length, 2 x 2-11/16 in. Size, Internal-2 in. diameter, NC Rolled Machine thread, 2 nuts, Hex nut type, 1-1/8 in. thread length, 2-11/16 in. height, 1-1/2 in. pipe diameter, 5/16 in. thread diameter
Product Type	1-1/2" U-Bolts Zinc Plated With Straps and Hex Nuts
Special Features	Features: U Bolts are Generally used to Support Conduit from Strut, Provided with Hex Nuts and Plate, NC Rolled Threads
Manufacturer Information	
Brand	LH DOTTIE
GTIN	00781002179306
Manufacturers Part Number	U150
UPC	781002179306
Taxonomies, Classifications, and G	Categories

U-Bolt

Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr. 75964-0000, TX Nacogdoches Phone: 936-569-7941 Fax: 936-560-4685

Packaging	
Carton	25
Weight Per each	0.194
Uses, Certifications, and Standards	
Application	Conduit