



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## TYPEA125100 1-1/4" NM Orange Type A Flex LT Conduit 100'

Abb Installation Products, Inc

|                  |   |
|------------------|---|
| Catalog Number   | TYPEA125100   |
| Manufacturer     | Abb Installation Products, Inc                            |
| Description      | 1-1/4 Inch Non-Metallic Orange Type A Liquidtight Conduit |
| Weight per unit  | 0.6940 (lbs/each)   |
| Product Category | Liquid Tight Conduit                                      |

### Material, Color, and Finish

|       |        |
|-------|--------|
| Color | Orange |
|-------|--------|

### Dimensions and Weight

|        |     |
|--------|-----|
| Length | 100 |
|--------|-----|

### Descriptions

|                        |   |
|------------------------|---|
| Also Known As...       | Carflex®<br>Liquid Tight Conduit                          |
| Description            | 1-1/4" NM ORANGE TYPE A FLEX LT CONDUIT 100'              |
| extra long description | ABB TYPEA125-100 1 1/4IN TYPE A LT                        |
| Long Description       | 1-1/4 Inch Non-metallic Orange Type A Liquidtight Conduit |
| Product Type           | 1 1/4IN Type A LT Conduit 100 Feet                        |
| similar brands         | Sealtite®   |
| Special Features       | No Metal Core to Fatigue from Flexing or Vibration        |

### Manufacturer Information

|                           |                 |
|---------------------------|-----------------|
| Brand                     | T&B Ind Fitting |
| GTIN                      | 00786210976747  |
| Manufacturers Part Number | TYPEA125-100    |
| UPC                       | 786210976747    |

### Taxonomies, Classifications, and Categories

|                      |   |
|----------------------|---|
| Category Description | NON-METALLIC SEALTITE AND FITTINGS      |
| Type                 | Type A-Non-Metallic Liquidtight Conduit |

### Trade Size

|            |          |
|------------|----------|
| Trade Size | 1-1/4 in |
|------------|----------|

### Availability

|             |     |
|-------------|-----|
| minimum qty | 100 |
|-------------|-----|

### Packaging

|                 |       |
|-----------------|-------|
| Carton          | 100   |
| Weight Per foot | 0.694 |

### Uses, Certifications, and Standards

|             |   |
|-------------|---|
| Application | Ideally Suited for Continuous Flexing Applications or Vibration |
| standard    | UL E95745   |