



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## U054 50A Surface Unmtrd

*Industrial Conn & Sol*

Catalog Number	U054
Manufacturer	Industrial Conn & Sol
Description	Midwest Electric's Temporary Power and Power Outlets Are A Means Of Providing Power Required By Various Construction Trades, Residential Sites, and Mobile Electrical Applications. Temporary Power and Power Outlets Offer One or More Receptacles, With or Without Overcurrent Protection, Disconnecting, Metering, and/or Pedestal Mounting Functions, In A Single Enclosure Of G-90 Zinc-Coated Steel. The Nema 3R Rainproof Enclosure Is Lockable and Engineered to Provide Maximum Protection Against Weather, Vandalis
Weight per unit	10.0 (lbs/each)
Product Category	Unmetered Power Outlet Panels

### Features

amperage rating	50
Cable Entry	Knockout Code (F): 1/2, 3/4 IN; Knockout Code (G): 1/2, 3/4, 1 IN; Knockout Code (H): 1/2, 3/4, 1, 1-1/4 IN
cutout size	5 X 7
Phase	1
Voltage Rating	120/240



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	50A SURFACE UNMTRD
extra long description	MIDWEST U054 MW 50A SURFACE UNMTRD
Long Description	Midwest Electric's Temporary Power and Power Outlets are a means of providing power required by various construction trades, residential sites, and mobile electrical applications. Temporary Power and Power Outlets offer one or more receptacles, with or without overcurrent protection, disconnecting, metering, and/or pedestal mounting functions, in a single enclosure of G-90 zinc-coated steel. The NEMA 3R rainproof enclosure is lockable and engineered to provide maximum protection against weather, vandalism
Product Type	MW 50A Surface Unmtrd
Special Features	G90 galvanized steel with superior electro-deposition paint finish, provides excellent corrosion protection All in one construction for factory assured terminations Rolled edge door for cord protection Cover design allows cords to exist while maintaining the NEMA 3R integrity Wide assortments of concentric knockouts offer flexibility in the installation All GFCI Duplexes are listed as weather resistant and tamper resistant as required by 2008 NEC in Article 406.8 and 406.11. Padlockable door to help prevent

## Manufacturer Information

Brand	MIDWEST
GTIN	00784567300185
Manufacturers Part Number	U054
UPC	784567300185

## Taxonomies, Classifications, and Categories

Category Description	TEMP. POWER PANELS & ACCESSORIES
Type	Unmetered Power Outlet

## Packaging

Carton	1
Package	4
Weight Per each	10

## Uses, Certifications, and Standards

standard	UL/cUL Listed
----------	---------------