

# Eaton U57

Catalog Number: U57

Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Feraloy iron alloy, U shape, 1-1/2"

## General specifications



Photo is representative

Product Name	Catalog Number
Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body	U57
	UPC
	662276465824
Product Length/Depth	Product Height
15.13 in	7.19 in
Product Width	Product Weight
2.88 in	6.2 lb

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

### NEMA Rating

3

4

12

## Product specifications

### Shape

U

### Trade size

1-1/2"

### Material

Feraloy iron alloy

## Resources

### 3D CAD drawing package

[Eaton Crouse-Hinds U57 3D drawing](#)

### Catalogs

[Crouse-Hinds series Form 7 catalog page](#)

### Certification reports

[Condulet Form 7 Conduit Outlet Bodies and Covers UL certification](#)

[Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification](#)

### Installation instructions

[IF 964 - Conduit Body Wire Pulling](#)

[IF 863 - Conduit Body Wire Pulling](#)

### Specifications and datasheets

[Eaton Specification Sheet - U57](#)

[Condulet Form 7 Industrial Grade Conduit Bodies](#)

### Technical service bulletins

[Industrial Fittings Bend Radius and Cubic Capacity Chart](#)

[Industrial Fittings Wire Fill Chart](#)

---

Reserved.

owners.

[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton U57

Catalog Number: U57

Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Feraloy iron alloy, U shape, 1-1/2"

## General specifications



Photo is representative

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body	U57
	<b>UPC</b>
	662276465824
<b>Product Length/Depth</b>	<b>Product Height</b>
15.13 in	7.19 in
<b>Product Width</b>	<b>Product Weight</b>
2.88 in	6.2 lb

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

### NEMA Rating

3

4

12

## Product specifications

### Shape

U

### Trade size

1-1/2"

### Material

Feraloy iron alloy

## Resources

### 3D CAD drawing package

[Eaton Crouse-Hinds U57 3D drawing](#)

### Catalogs

[Crouse-Hinds series Form 7 catalog page](#)

### Certification reports

[Condulet Form 7 Conduit Outlet Bodies and Covers UL certification](#)

[Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification](#)

### Installation instructions

[IF 964 - Conduit Body Wire Pulling](#)

[IF 863 - Conduit Body Wire Pulling](#)

### Specifications and datasheets

[Eaton Specification Sheet - U57](#)

[Condulet Form 7 Industrial Grade Conduit Bodies](#)

### Technical service bulletins

[Industrial Fittings Bend Radius and Cubic Capacity Chart](#)

[Industrial Fittings Wire Fill Chart](#)

---

Reserved.

owners.

[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)