

# Specifications



## Eaton UBTH4330TCH

Eaton meter socket, 1-pos commercial or resi service, 320A, Over/under, Large hub open, 3/8 inch stud, 4-jaw, 1-ph, 3/8 inch stud, Barrel lock, Lever bypass, 3-wire, Ringless, 600 Vac

### General specifications

<b>PRODUCT NAME</b>	Eaton meter socket
<b>CATALOG NUMBER</b>	UBTH4330TCH
<b>UPC</b>	786685135472
<b>PRODUCT LENGTH/DEPTH</b>	5.69 in
<b>PRODUCT HEIGHT</b>	36.63 in
<b>PRODUCT WIDTH</b>	15 in
<b>PRODUCT WEIGHT</b>	38 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>CERTIFICATIONS</b>	UL Listed



Powering Business Worldwide

## Product specifications

<b>SPECIAL FEATURES</b>	Barrel lock provisions
<b>TYPE</b>	Single-position commercial or residential service
<b>AMPERAGE RATING</b>	320A
<b>FEED TYPE</b>	Top/bottom
<b>NUMBER OF JAWS</b>	Four-jaw
<b>PHASE</b>	Single-phase
<b>UTILITY APPROVALS</b>	TN : Nashville Electric Service
<b>LINE</b>	3/8 in stud
<b>LOAD</b>	3/8 in stud
<b>NUMBER OF WIRES</b>	Three-wire
<b>HUB TYPE</b>	5 x 5 hub opening
<b>SECURITY</b>	Ringless
<b>VOLTAGE RATING</b>	600 V
<b>BYPASS</b>	Lever
<b>NUMBER OF SOCKETS</b>	1

## Resources

<b>CATALOGS</b>	<a href="#">Residential and Light Commercial, Metering Products, Volume 1 Tab 4</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - UBTH4330TCH</a>

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.



# Specifications



## Eaton UBTH4330TCH

Eaton meter socket, 1-pos commercial or resi service, 320A, Over/under, Large hub open, 3/8 inch stud, 4-jaw, 1-ph, 3/8 inch stud, Barrel lock, Lever bypass, 3-wire, Ringless, 600 Vac

### General specifications

<b>PRODUCT NAME</b>	Eaton meter socket
<b>CATALOG NUMBER</b>	UBTH4330TCH
<b>UPC</b>	786685135472
<b>PRODUCT LENGTH/DEPTH</b>	5.69 in
<b>PRODUCT HEIGHT</b>	36.63 in
<b>PRODUCT WIDTH</b>	15 in
<b>PRODUCT WEIGHT</b>	38 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>CERTIFICATIONS</b>	UL Listed

## Product specifications

<b>SPECIAL FEATURES</b>	Barrel lock provisions
<b>TYPE</b>	Single-position commercial or residential service
<b>AMPERAGE RATING</b>	320A
<b>FEED TYPE</b>	Top/bottom
<b>NUMBER OF JAWS</b>	Four-jaw
<b>PHASE</b>	Single-phase
<b>UTILITY APPROVALS</b>	TN : Nashville Electric Service
<b>LINE</b>	3/8 in stud
<b>LOAD</b>	3/8 in stud
<b>NUMBER OF WIRES</b>	Three-wire
<b>HUB TYPE</b>	5 x 5 hub opening
<b>SECURITY</b>	Ringless
<b>VOLTAGE RATING</b>	600 V
<b>BYPASS</b>	Lever
<b>NUMBER OF SOCKETS</b>	1

## Resources

<b>CATALOGS</b>	<a href="#">Residential and Light Commercial, Metering Products, Volume 1 Tab 4</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - UBTH4330TCH</a>

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.

