



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## UC109 1/2"R, 1/4"P, 250-2/Ocbl Ugrn Clamp

*Nsi Industries*

|                  |   |
|------------------|---|
| Catalog Number   | UC109   |
| Manufacturer     | Nsi Industries  |
| Description      | The Nsi Uc-109 Bronze Heavy Duty U-Bolt Clamp Is Designed to Grip 7/8" to 1" Rods and Ground 1/2" to 3/4" Ips Pipes In Parallel or 90-Degree Positions With An Easily Adjusted, Durably Strong Design. The High-Copper-Content Alloy Of The Clamp Provides Excellent Conductivity and Heavy-Duty Strength, Alongside The Silicon Bronze Nuts and Lockwashers. Use This U-Bolt For Demanding Applications In Harsh Environments, Including Direct Burial In Earth or Concrete. Ul Listed 467 For Grounding and Bonding. Stock PR |
| Weight per unit  | 0.7300 (lbs/each)   |
| Product Category | Ground Rods & Grounding System  |

### Features

|          |        |
|----------|--------|
| Warranty | 1 YEAR |
|----------|--------|

### Material, Color, and Finish

|                     |                   |
|---------------------|-------------------|
| Clamp Material      | 250 MCM - 2/0 AWG |
| Insulation Material | Silicon Bronze    |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |   |
|------------------------|---|
| Description            | 1/2"R,1/4"P,250-2/OCBL UGRN CLAMP   |
| extra long description | NSI UC-109 U Bolt Ground Clamp 1 Co   |
| Features               | NSI grounding and bonding products rise to the occasion in a wide variety of professional environments with excellent material quality and flexible designs. These heavy-duty bronze U-bolt clamps offer a durable and reliable solution for connecting a ground cable to a pipe, using the adjustable clamping structure. The gripping jaws feature a flexible design that fits a range of pipe sizes and can attach the grounding rod and pipe either in parallel or at a 90-degree angle. The bronze body has a high copper  |
| Long Description       | The NSI UC-109 Bronze Heavy Duty U-Bolt Clamp is designed to grip 7/8" to 1" rods and ground 1/2" to 3/4" IPS pipes in parallel or 90-degree positions with an easily adjusted, durably strong design. The high-copper-content alloy of the clamp provides excellent conductivity and heavy-duty strength, alongside the silicon bronze nuts and lockwashers. Use this U-bolt for demanding applications in harsh environments, including direct burial in earth or concrete. UL Listed 467 for Grounding and Bonding. Stock pr |
| Product Type           | U Bolt Ground Clamp 1 Cond. 250-2/0   |
| Special Features       | 7/8-1 Rod Size - 1/2-3/4 Pipe Size  |

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | NSi            |
| GTIN                      | 00662381108067 |
| Manufacturers Part Number | UC-109         |
| UPC                       | 662381108067   |

## Taxonomies, Classifications, and Categories

|                      |  |
|----------------------|--|
| Category Description | SERVICE ENTRANCE FITTINGS: Weatherheads & Grounding Fittings & Ground Rods |
| Type                 | Heavy Duty Ground Connector For Parrallel Copper Cables                    |

## Packaging

|                 |      |
|-----------------|------|
| Carton          | 12   |
| Weight Per each | 0.73 |

## Uses, Certifications, and Standards

|             |                |
|-------------|----------------|
| Application | Grounding Wire |
| standard    | UL467          |