



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



UC109 1/2"R, 1/4"P, 250-2/Ocbl Ugrn Clamp

Nsi Industries

| | |
|------------------|---|
| Catalog Number | UC109 |
| Manufacturer | Nsi Industries |
| Description | The Nsi Uc-109 Bronze Heavy Duty U-Bolt Clamp Is Designed to Grip 7/8" to 1" Rods and Ground 1/2" to 3/4" Ips Pipes In Parallel or 90-Degree Positions With An Easily Adjusted, Durably Strong Design. The High-Copper-Content Alloy Of The Clamp Provides Excellent Conductivity and Heavy-Duty Strength, Alongside The Silicon Bronze Nuts and Lockwashers. Use This U-Bolt For Demanding Applications In Harsh Environments, Including Direct Burial In Earth or Concrete. Ul Listed 467 For Grounding and Bonding. Stock PR |
| Weight per unit | 0.7300 (lbs/each) |
| Product Category | Ground Rods & Grounding System |

Features

| | |
|----------|--------|
| Warranty | 1 YEAR |
|----------|--------|

Material, Color, and Finish

| | |
|---------------------|-------------------|
| Clamp Material | 250 MCM - 2/0 AWG |
| Insulation Material | Silicon Bronze |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Description | 1/2"R,1/4"P,250-2/OCBL UGRN CLAMP |
| extra long description | NSI UC-109 U Bolt Ground Clamp 1 Co |
| Features | NSI grounding and bonding products rise to the occasion in a wide variety of professional environments with excellent material quality and flexible designs. These heavy-duty bronze U-bolt clamps offer a durable and reliable solution for connecting a ground cable to a pipe, using the adjustable clamping structure. The gripping jaws feature a flexible design that fits a range of pipe sizes and can attach the grounding rod and pipe either in parallel or at a 90-degree angle. The bronze body has a high copper |
| Long Description | The NSI UC-109 Bronze Heavy Duty U-Bolt Clamp is designed to grip 7/8" to 1" rods and ground 1/2" to 3/4" IPS pipes in parallel or 90-degree positions with an easily adjusted, durably strong design. The high-copper-content alloy of the clamp provides excellent conductivity and heavy-duty strength, alongside the silicon bronze nuts and lockwashers. Use this U-bolt for demanding applications in harsh environments, including direct burial in earth or concrete. UL Listed 467 for Grounding and Bonding. Stock pr |
| Product Type | U Bolt Ground Clamp 1 Cond. 250-2/0 |
| Special Features | 7/8-1 Rod Size - 1/2-3/4 Pipe Size |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | NSi |
| GTIN | 00662381108067 |
| Manufacturers Part Number | UC-109 |
| UPC | 662381108067 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | SERVICE ENTRANCE FITTINGS: Weatherheads & Grounding Fittings & Ground Rods |
| Type | Heavy Duty Ground Connector For Parrallel Copper Cables |

Packaging

| | |
|-----------------|------|
| Carton | 12 |
| Weight Per each | 0.73 |

Uses, Certifications, and Standards

| | |
|-------------|----------------|
| Application | Grounding Wire |
| standard | UL467 |