



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

7604 Gateway Blvd
77521-0000, TX Baytown
Phone: 832-514-7819
Fax: 832-514-7820



UC109 1/2"R, 1/4"P, 250-2/Ocbl Ugrn Clamp

Nsi Industries

Catalog Number	UC109
Manufacturer	Nsi Industries
Description	The Nsi Uc-109 Bronze Heavy Duty U-Bolt Clamp Is Designed to Grip 7/8" to 1" Rods and Ground 1/2" to 3/4" Ips Pipes In Parallel or 90-Degree Positions With An Easily Adjusted, Durably Strong Design. The High-Copper-Content Alloy Of The Clamp Provides Excellent Conductivity and Heavy-Duty Strength, Alongside The Silicon Bronze Nuts and Lockwashers. Use This U-Bolt For Demanding Applications In Harsh Environments, Including Direct Burial In Earth or Concrete. Ul Listed 467 For Grounding and Bonding. Stock PR
Weight per unit	0.7300 (lbs/each)
Product Category	Ground Rods & Grounding System

Features

Warranty	1 YEAR
----------	--------

Material, Color, and Finish

Clamp Material	250 MCM - 2/0 AWG
Insulation Material	Silicon Bronze



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

7604 Gateway Blvd
77521-0000, TX Baytown
Phone: 832-514-7819
Fax: 832-514-7820

Descriptions

Description	1/2"R,1/4"P,250-2/OCBL UGRN CLAMP
extra long description	NSI UC-109 U Bolt Ground Clamp 1 Co
Features	NSI grounding and bonding products rise to the occasion in a wide variety of professional environments with excellent material quality and flexible designs. These heavy-duty bronze U-bolt clamps offer a durable and reliable solution for connecting a ground cable to a pipe, using the adjustable clamping structure. The gripping jaws feature a flexible design that fits a range of pipe sizes and can attach the grounding rod and pipe either in parallel or at a 90-degree angle. The bronze body has a high copper
Long Description	The NSI UC-109 Bronze Heavy Duty U-Bolt Clamp is designed to grip 7/8" to 1" rods and ground 1/2" to 3/4" IPS pipes in parallel or 90-degree positions with an easily adjusted, durably strong design. The high-copper-content alloy of the clamp provides excellent conductivity and heavy-duty strength, alongside the silicon bronze nuts and lockwashers. Use this U-bolt for demanding applications in harsh environments, including direct burial in earth or concrete. UL Listed 467 for Grounding and Bonding. Stock pr
Product Type	U Bolt Ground Clamp 1 Cond 250-2/0
Special Features	7/8-1 Rod Size - 1/2-3/4 Pipe Size

Manufacturer Information

Brand	Polaris
GTIN	00662381108067
Manufacturers Part Number	UC-109
UPC	662381108067

Taxonomies, Classifications, and Categories

Category Description	SERVICE ENTRANCE FITTINGS: Weatherheads & Grounding Fittings & Ground Rods
Type	Heavy Duty Ground Connector For Parrallel Copper Cables

Packaging

Carton	12
Weight Per each	0.73

Uses, Certifications, and Standards

Application	Grounding Wire
standard	UL467