



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



UCES24INSWW690CR 24" 11W Led Undercab 27K/3K/35K Select 620LM *Lithonia Lighting - Acuity*

Catalog Number	UCES24INSWW690CR
Manufacturer	Lithonia Lighting - Acuity
Description	Lith Uces 24IN SWW6 90CRI WH M6 Eco
Weight per unit	1.5 (lbs/each)
Product Category	Lighting

Features

average life	50,000
dimensions	24 x 2.55 x 1.07
dimnable	Yes
Hardware	Yes
Lamp Included	Yes
Lamp Type	LED - Static
Material	Steel
Maximum Operating Temperature	25
Number of Lamps	1
Power Source	Hardwired
Shape	Rectangular
Voltage Rating	120
Warranty	5
Wattage	10.6

Material, Color, and Finish

Color	White
color rendering index (cri)	90
color temperature	2700 ,3000 ,3500 ,Variable
Finish	Gloss
Lens Color	WHITE
Lens Material	Acrylic
Style	CONTEMPORARY

Dimensions and Weight

Height	1.07
Length	24
Width	2.55

Descriptions

Description	24" 11W LED UNDERCAB 27K/3K/35K SELECT 620LM
Features	Contractor Select
Long Description	LITH UCES 24IN SWW6 90CRI WH M6 Eco
Product Type	Undercabinet



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	JUNO
GTIN	00196182177422
Manufacturers Part Number	UCES 24IN SWW6 90CRI WH M6
UPC	196182177422

Taxonomies, Classifications, and Categories

Category Description	LED TRACK, RAIL, TASK & UNDERCABINET LIGHTING
Type	Undercabinet

Availability

Manufacturer Status	Inactive
---------------------	----------

Packaging

Carton	1
Package	6
Weight	1.5
Weight Per each	1.5

Uses, Certifications, and Standards

Application	Hospitality,Residential,Retail
environmental conditions	Indoor
Mounting	SURFACE
standard	cULCA Title 24,ENERGY STAR,JA8