

# Enclosures

## SINGLE RESIDENCE SERVICE ENCLOSURES

- 18GA Galvanize Steel
- Captive Cover Screws
- Screw/Nail Holes on Sides
- Open back to simplify splitter mounting and connection before installation of service box.



Cat. No.	Features	Dimension (Excluding Bracket)				Color	Std. Pkg.
		Width	Height	Depth	Cu. In.		
<b>UM1020-TV</b>	With Embossed "TELEVISION" Text	14-7/8"	4-5/8"	1-5/8"	111.8	Beige	10
<b>UM900-TV</b>	With Embossed "TV" Text	3-3/4"	7"	2"	52.5	Beige	20
<b>UM1020-PH</b>	With Embossed "TELEPHONE" Text & Protector Bracket	14-7/8"	4-5/8"	2-7/8"	197.8	Beige	10
<b>UM900-PH</b>	With Embossed "PHONE" Text	3-3/4"	7"	2"	52.5	Beige	20


NEMA Enclosures



UM1020-TV



UM900-TV



UM1020-PH



UM900-PH

## MODULAR INTERFACE SERVICE ENCLOSURES


- 18GA Galvanize Steel
- 2 Captive Cover Screws
- 9 Screw/Nail Holes on Sides
- Plywood back to simplify protector mounting and connection before installation of service box.



Cat. No.	Description	Dimension (Excluding Bracket)				Color	Std. Pkg.
		Width	Height	Depth	Cu. In.		
<b>UM1100-TV</b>	With Embossed "TELEVISION" Text & Plywood Back Bracket	14-7/8"	11"	4-7/8"	797.6	Beige	5
<b>UM1100-PH</b>	With Embossed "TELEPHONE" Text & Plywood Back Bracket	14-7/8"	11"	4-7/8"	797.6	Beige	5
<b>UM1100-PH-GB</b>	With Embossed "TELEPHONE" Text & Plywood Back Bracket <b>With Installed Ground Bar</b>	14-7/8"	11"	4-7/8"	797.6	Beige	5



UM1100-TV



UM1100-PH  
UM1100-PH-GB

### Certification:

- File 33033655

# Enclosures

## SINGLE RESIDENCE SERVICE ENCLOSURES

- 18GA Galvanize Steel
- Captive Cover Screws
- Screw/Nail Holes on Sides
- Open back to simplify splitter mounting and connection before installation of service box.



Cat. No.	Features	Dimension (Excluding Bracket)				Color	Std. Pkg.
		Width	Height	Depth	Cu. In.		
<b>UM1020-TV</b>	With Embossed "TELEVISION" Text	14-7/8"	4-5/8"	1-5/8"	111.8	Beige	10
<b>UM900-TV</b>	With Embossed "TV" Text	3-3/4"	7"	2"	52.5	Beige	20
<b>UM1020-PH</b>	With Embossed "TELEPHONE" Text & Protector Bracket	14-7/8"	4-5/8"	2-7/8"	197.8	Beige	10
<b>UM900-PH</b>	With Embossed "PHONE" Text	3-3/4"	7"	2"	52.5	Beige	20


NEMA Enclosures



UM1020-TV



UM900-TV



UM1020-PH



UM900-PH

## MODULAR INTERFACE SERVICE ENCLOSURES


- 18GA Galvanize Steel
- 2 Captive Cover Screws
- 9 Screw/Nail Holes on Sides
- Plywood back to simplify protector mounting and connection before installation of service box.



Cat. No.	Description	Dimension (Excluding Bracket)				Color	Std. Pkg.
		Width	Height	Depth	Cu. In.		
<b>UM1100-TV</b>	With Embossed "TELEVISION" Text & Plywood Back Bracket	14-7/8"	11"	4-7/8"	797.6	Beige	5
<b>UM1100-PH</b>	With Embossed "TELEPHONE" Text & Plywood Back Bracket	14-7/8"	11"	4-7/8"	797.6	Beige	5
<b>UM1100-PH-GB</b>	With Embossed "TELEPHONE" Text & Plywood Back Bracket <b>With Installed Ground Bar</b>	14-7/8"	11"	4-7/8"	797.6	Beige	5



UM1100-TV



UM1100-PH  
UM1100-PH-GB

### Certification:

- File 33033655