



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## URTRS202BCH 200A 10 Ring Type Meter Socket

*Eaton Corp*

Catalog Number	URTRS202BCH
Manufacturer	Eaton Corp
Description	Eaton Meter Socket, 3-5/16 Hub Opening, 200A, Overhead/Underground, #8-250 Kcmil, Four-Jaw, Single-Phase, #8-250 Kcmil, Sockets:1, Three-Wire, Ring, 600V
Weight per unit	1.0 (lbs/each)
Product Category	Residential Single Meter Socket

### Features

amperage rating	200A
dimensions	4.3800 IN X 8.0000 IN X 14.0000 IN
Phase	Single-phase
Voltage Rating	600 V

### Descriptions

Also Known As...	Meter Socket Meter Box
Description	200A 10 RING TYPE METER SOCKET
extra long description	ETN URTRS202BCH 200A 10 RING TYPE M
Features	Eaton is your one-stop shop for the widest range of residential and light commercial electric meter sockets in the industry. These single-socket surface- or flush-mount outdoor enclosures come in two styles, allowing for both easy, cost-saving installation, and for the use of BR- or CH-type branch breakers. The one-piece, die-run electric meter socket enclosures eliminate tampering and extend product life. These are utility approved and can be used for residential meter socket installations, rural service
Long Description	Eaton meter socket, 3-5/16 Hub opening, 200A, Overhead/underground, #8-250 kcmil, Four-jaw, Single-phase, #8-250 kcmil, Sockets:1, Three-wire, Ring, 600V
Product Type	200A 10 Ring Type Meter Socket

### Manufacturer Information

Brand	Eaton
GTIN	00782114114339
Manufacturers Part Number	URTRS202BCH
UPC	782114114339

### Taxonomies, Classifications, and Categories

Category Description	Meter Sockets
Type	Meter socket



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	1

## Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies and EOEMs - Other
standard	UL Listed