

# Eaton URTRS223ACH

Catalog Number: URTRS223ACH

Eaton meter socket, Solid top, 200A, Underground, Solid top, #8-350 kcmil, Four-jaw, Single-phase, #8-350 kcmil, Sockets:1, Three-wire, Ring, 600V

## General specifications



### Product Name

Eaton meter socket

### Catalog Number

URTRS223ACH

### UPC

786685125428

### Product Length/Depth

4.93 in

### Product Height

13 in

### Product Width

13 in

### Product Weight

13 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

UL Listed

## Product specifications

### Type

Solid top

### Amperage Rating

200A

### Feed type

Bottom

### Number of jaws

Four-jaw

### Phase

Single-phase

### Utility approvals

TN : Knoxville Utility Board (KUB)

### Line

#8-350 kcmil

### Load

#8-350 kcmil

### Number of wires

Three-wire

### Hub type

Solid top

### Security

Ring

### Voltage rating

600 V

### Number of sockets

1

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - URTRS223ACH](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton URTRS223ACH

Catalog Number: URTRS223ACH

Eaton meter socket, Solid top, 200A, Underground, Solid top, #8-350 kcmil, Four-jaw, Single-phase, #8-350 kcmil, Sockets:1, Three-wire, Ring, 600V

## General specifications



### Product Name

Eaton meter socket

### Catalog Number

URTRS223ACH

### UPC

786685125428

### Product Length/Depth

4.93 in

### Product Height

13 in

### Product Width

13 in

### Product Weight

13 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

UL Listed

## Product specifications

### Type

Solid top

### Amperage Rating

200A

### Feed type

Bottom

### Number of jaws

Four-jaw

### Phase

Single-phase

### Utility approvals

TN : Knoxville Utility Board (KUB)

### Line

#8-350 kcmil

### Load

#8-350 kcmil

### Number of wires

Three-wire

### Hub type

Solid top

### Security

Ring

### Voltage rating

600 V

### Number of sockets

1

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - URTRS223ACH](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)