

# Specifications



## Eaton UTE7213TCH

Eaton meter socket, Comm, 200A, Over/under, 5x5 inch hub open, #6-350 kcmil, 7-jaw, 3-ph, #6-350 kcmil, Lever bypass, Gnd con (#14-#2 Cu), Triplex, Four-wire, Ringless, 600 Vac

### General specifications

<b>PRODUCT NAME</b>	Eaton meter socket
<b>CATALOG NUMBER</b>	UTE7213TCH
<b>UPC</b>	786685351261
<b>PRODUCT LENGTH/DEPTH</b>	4.94 in
<b>PRODUCT HEIGHT</b>	19 in
<b>PRODUCT WIDTH</b>	13 in
<b>PRODUCT WEIGHT</b>	25 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>CERTIFICATIONS</b>	UL Listed

### Product specifications

<b>TYPE</b>	Commercial
<b>AMPERAGE RATING</b>	200A
<b>FEED TYPE</b>	Top/bottom
<b>NUMBER OF JAWS</b>	Seven-jaw
<b>PHASE</b>	Three-phase

NY : Central Hudson Gas & Electric (CHG&E)  
 ME : Central Maine Power  
 OH : Dayton Power and Light (DP&L)  
 MD : First Energy (Potomac Edison)  
 VA : First Energy (Potomac Edison)  
 WV : First Energy (Mon Power)  
 NJ : First Energy (Jersey Central Power and Light)  
 OH : First Energy (Ohio Edison, Toledo Edison, The Illuminating Company)  
 PA : First Energy (Allegheny Power, MET ED, Penelec, West Penn Power)  
 WI : WE Energies / Wisconsin Public Service (WPS)  
 SC : South Carolina Electric and

### UTILITY APPROVALS

# Specifications



## Eaton UTE7213TCH

Eaton meter socket, Comm, 200A, Over/under, 5x5 inch hub open, #6-350 kcmil, 7-jaw, 3-ph, #6-350 kcmil, Lever bypass, Gnd con (#14-#2 Cu), Triplex, Four-wire, Ringless, 600 Vac

### General specifications

<b>PRODUCT NAME</b>	Eaton meter socket
<b>CATALOG NUMBER</b>	UTE7213TCH
<b>UPC</b>	786685351261
<b>PRODUCT LENGTH/DEPTH</b>	4.94 in
<b>PRODUCT HEIGHT</b>	19 in
<b>PRODUCT WIDTH</b>	13 in
<b>PRODUCT WEIGHT</b>	25 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>CERTIFICATIONS</b>	UL Listed

### Product specifications

<b>TYPE</b>	Commercial
<b>AMPERAGE RATING</b>	200A
<b>FEED TYPE</b>	Top/bottom
<b>NUMBER OF JAWS</b>	Seven-jaw
<b>PHASE</b>	Three-phase

NY : Central Hudson Gas & Electric (CHG&E)  
 ME : Central Maine Power  
 OH : Dayton Power and Light (DP&L)  
 MD : First Energy (Potomac Edison)  
 VA : First Energy (Potomac Edison)  
 WV : First Energy (Mon Power)  
 NJ : First Energy (Jersey Central Power and Light)  
 OH : First Energy (Ohio Edison, Toledo Edison, The Illuminating Company)  
 PA : First Energy (Allegheny Power, MET ED, Penelec, West Penn Power)  
 WI : WE Energies / Wisconsin Public Service (WPS)  
 SC : South Carolina Electric and

### UTILITY APPROVALS