

# Eaton UTH7330UCH

Catalog Number: UTH7330UCH

Eaton meter socket, 1-pos commercial or resi service, 320A, Over/under, 5x5 inch hub cover plate, 3/8 inch stud, 7-jaw, three-phase, 3/8 inch stud, Lever bypass, Gnd conn (#14-#2 Cu), Triplex, 4-wire, Ringless, 600 Vac



## General specifications

Product Name	Catalog Number
Eaton meter socket	UTH7330UCH
UPC	Product Length/Depth
782116016686	6.5 in
Product Height	Product Width
39.88 in	20 in
Product Weight	Warranty
60 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Certifications	
UL Listed	

defaultTaxonomyAttributeLabel	Resources
Type	Brochures
Single-position commercial or residential service	Single Meter Sockets
Amperage Rating	Catalogs
320A	Eaton's Volume 1—Residential and Light Commercial
Feed type	Specifications and datasheets
Top/bottom	Eaton Specification Sheet - UTH7330UCH
Number of jaws	Metering Equipment - Utilities Servicing Wisconsin and Minnesota
Seven-jaw	Warranty guides
Phase	Selling Policy 25-000 - Distribution and Control Products and Services
Three-phase	
Utility approvals	
ME : Central Maine Power	
NM : El Paso Electric	
TX : El Paso Electric	
AR : Entergy	
LA : Entergy	
MS : Entergy	
TX : Entergy	
KY : Louisville Gas & Electric/Kentucky Utilities	
TN : Middle Tennessee EMC	
Line	
3/8 in stud	
Load	
3/8 in stud	
Number of wires	
Four-wire	
Hub type	
5 x 5 hub cover plate	
Security	
Ringless	
Voltage rating	
600 V	
Bypass	
Lever	
Number of sockets	
1	



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are  
property of their respective  
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton UTH7330UCH

Catalog Number: UTH7330UCH

Eaton meter socket, 1-pos commercial or resi service, 320A, Over/under, 5x5 inch hub cover plate, 3/8 inch stud, 7-jaw, three-phase, 3/8 inch stud, Lever bypass, Gnd conn (#14-#2 Cu), Triplex, 4-wire, Ringless, 600 Vac



## General specifications

Product Name	Catalog Number
Eaton meter socket	UTH7330UCH
UPC	Product Length/Depth
782116016686	6.5 in
Product Height	Product Width
39.88 in	20 in
Product Weight	Warranty
60 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Certifications	
UL Listed	

## defaultTaxonomyAttributeLabel

### Type

Single-position commercial or residential service

### Amperage Rating

320A

### Feed type

Top/bottom

### Number of jaws

Seven-jaw

### Phase

Three-phase

### Utility approvals

ME : Central Maine Power

NM : El Paso Electric

TX : El Paso Electric

AR : Entergy

LA : Entergy

MS : Entergy

TX : Entergy

KY : Louisville Gas & Electric/Kentucky Utilities

TN : Middle Tennessee EMC

### Line

3/8 in stud

### Load

3/8 in stud

### Number of wires

Four-wire

### Hub type

5 x 5 hub cover plate

### Security

Ringless

### Voltage rating

600 V

### Bypass

Lever

### Number of sockets

1

## Resources

### Brochures

[Single Meter Sockets](#)

### Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

### Specifications and datasheets

[Eaton Specification Sheet - UTH7330UCH](#)

[Metering Equipment - Utilities Servicing Wisconsin and Minnesota](#)

### Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are  
property of their respective  
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)