

Eaton UTRS101BE

Catalog Number: UTRS101BE

Eaton meter socket, 1-pos resi service, 125 A, Over, 3-5/16 inch hub open, #8-2/0 AWG, 4-jaw, 1-phase, #8-2/0 AWG, Gnd conn (#14-#2 Cu), Triplex, 3-wire, Ringless, 600 Vac



General specifications

Product Name

Eaton meter socket

Catalog Number

UTRS101BE

UPC

786685217710

Product Length/Depth

3.61 in

Product Height

11.05 in

Product Width

8.22 in

Product Weight

6.46 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

Product specifications

Type

Single-position residential service

Amperage Rating

125A

Feed type

Overhead

Number of jaws

Four-jaw

Phase

Single-phase

Utility approvals

ME : Central Maine Power

NM : El Paso Electric

TX : El Paso Electric

AL : Alabama Power

ME : Emera Maine (Bangor Hydro Electric Co./ Maine Public Service Company)

MO : Empire District Electric

OK : Empire District Electric

AR : Entergy

LA : Entergy

MS : Entergy

TX : Entergy

AL : Huntsville Utilities

FL : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

IN : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

KY : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

NC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

OH : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

SC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

TX : Pedernales Electric Cooperative

NM : Public Service Company of New Mexico (PNM)

SC : South Carolina Electric and Gas (SCE&G)

Line

#8-2/0 AWG

Resources

Catalogs

[Residential and Light Commercial, Metering Products, Volume 1 Tab 4](#)

Specifications and datasheets

[Eaton Specification Sheet - UTRS101BE](#)

Load

#8-2/0 AWG

Number of wires

Three-wire

Hub type

3-5/16 in hub opening

Connection

Ground connection

Security

Ringless

Voltage rating

600 V

Number of sockets

1



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia

Eaton UTRS101BE

Catalog Number: UTRS101BE

Eaton meter socket, 1-pos resi service, 125 A, Over, 3-5/16 inch hub open, #8-2/0 AWG, 4-jaw, 1-phase, #8-2/0 AWG, Gnd conn (#14-#2 Cu), Triplex, 3-wire, Ringless, 600 Vac



General specifications

Product Name

Eaton meter socket

Catalog Number

UTRS101BE

UPC

786685217710

Product Length/Depth

3.61 in

Product Height

11.05 in

Product Width

8.22 in

Product Weight

6.46 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

Product specifications

Type

Single-position residential service

Amperage Rating

125A

Feed type

Overhead

Number of jaws

Four-jaw

Phase

Single-phase

Utility approvals

ME : Central Maine Power

NM : El Paso Electric

TX : El Paso Electric

AL : Alabama Power

ME : Emera Maine (Bangor Hydro Electric Co./ Maine Public Service Company)

MO : Empire District Electric

OK : Empire District Electric

AR : Entergy

LA : Entergy

MS : Entergy

TX : Entergy

AL : Huntsville Utilities

FL : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

IN : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

KY : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

NC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

OH : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

SC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

TX : Pedernales Electric Cooperative

NM : Public Service Company of New Mexico (PNM)

SC : South Carolina Electric and Gas (SCE&G)

Line

#8-2/0 AWG

Resources

Catalogs

[Residential and Light Commercial, Metering Products, Volume 1 Tab 4](#)

Specifications and datasheets

[Eaton Specification Sheet - UTRS101BE](#)

Load

#8-2/0 AWG

Number of wires

Three-wire

Hub type

3-5/16 in hub opening

Connection

Ground connection

Security

Ringless

Voltage rating

600 V

Number of sockets

1



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia