

Specifications



Eaton UTRS213BE

Eaton meter socket, 1-pos resi service, 200 A, Over/under, 3-5/16 inch hub open, #6-350 kcmil, 4-jaw, 1-ph, #6-350 kcmil, Gnd conn (#14-#2 Cu), Triplex, 3-wire, Ringless, 600 Vac

General specifications

PRODUCT NAME	Eaton meter socket
CATALOG NUMBER	UTRS213BE
UPC	786685217758
PRODUCT LENGTH/DEPTH	4.48 in
PRODUCT HEIGHT	15.11 in
PRODUCT WIDTH	11.22 in
PRODUCT WEIGHT	14 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed

Product specifications	
TYPE	Single-position residential service
AMPERAGE RATING	200A
FEED TYPE	Top/bottom
NUMBER OF JAWS	Four-jaw
PHASE	Single-phase
UTILITY APPROVALS	ME : Central Maine Power MI : DTE Energy (Detroit Edison) MO : Empire District Electric OK : Empire District Electric AR : Entergy LA : Entergy MS : Entergy TX : Entergy TN : Knoxville Utility Board (KUB) TX : Oncor NM : Public Service Company of New Mexico (PNM) CT : United Illuminating (UI) SC : South Carolina Electric and Gas (SCE&G) NM : Texas-New Mexico Power (TNMP) TX : Texas-New Mexico Power (TNMP)
LINE	#6-350 kcmil
LOAD	#6-350 kcmil
NUMBER OF WIRES	Three-wire
HUB TYPE	3-5/16 in hub opening
SECURITY	Ringless
VOLTAGE RATING	600 V
NUMBER OF SOCKETS	1

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:

Resources	
CATALOGS	Residential and Light Commercial, Metering Products, Volume 1 Tab 4
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - UTRS213BE
WARRANTY GUIDES	Selling Policy 25-000 - Distribution and Control Products and Services



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights
Reserved.

Eaton is a registered trademark.

All other trademarks are property of
their respective owners.

Follow us on social media to get the latest
product and support information.

