




ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



V2003 STL Support Clip 2000 Iv

Wiremold/Legrand

Catalog Number	V2003
Manufacturer	Wiremold/Legrand
Description	<P>Supports Lengths Of 2000 Series Raceway At Any Point Desired. Mounts to Surface With No. 6 Flathead Screw. This Support Clip Has Plated Finish. V Indicates Ivory Finish.</P>
Weight per unit	0.0300 (lbs/each)
Product Category	Metallic Raceway & Accessories

Features

Enclosure Type	Steel
Voltage	125.0 V

Descriptions

Description	STL SUPPORT CLIP 2000 IV
extra long description	WM V2003 STL SUPPORT CLIP 2000 IVOR
Long Description	<p>Supports lengths of 2000 Series Raceway at any point desired. Mounts to surface with No. 6 flathead screw. This support clip has plated finish. V indicates Ivory finish.</p>
Product Type	STL Support Clip 2000 Ivory
Special Features	Steel Raceway, Compact low profile design, Full range of fittings, one and two - gang device boxes.

Manufacturer Information

Brand	WIREMOLD
GTIN	00786776189780
Manufacturers Part Number	V2003
UPC	786776189780

Taxonomies, Classifications, and Categories

Category Description	Panduit & Wiremold Metallic & Non-Metallic Raceways
Type	Plugmold

Trade Size

Amperage	15.0
----------	------

Packaging

Carton	10
Weight Per each	0.03



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

standard

ROHS, NAFTA, CULUS, cULus Listed Base & Blank Cover: File E4376 Guide RJBT. Multioutlet Assemblies: File E15191 Guide PVGT. Fittings: File E41751 Guide RJPR. Base & Blank Cover & Plugmold Series w/Snapicoil Haarness: Meets Article 386 of NEC. Meets Section 12-3032 of CEC. cULus Listed Raceway: File E4376 Guide RJBT. Fittings: File E41751 Guide RJPR. Base & Black Cover: Meets Article 386 of NEC. Meets Section 12-600 of CEC.
