

Specifications



Photo is representative

Eaton V65W-G

Eaton Crouse-Hinds series V-Spring telescoping light pole, Galvanized steel, Wall mount

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series V-Spring telescoping light pole
CATALOG NUMBER	V65W-G
UPC	662276470019
PRODUCT LENGTH/DEPTH	73.5 in
PRODUCT HEIGHT	6.57 in
PRODUCT WIDTH	6.57 in
PRODUCT WEIGHT	53 lb



Certifications and compliances

AREA CLASSIFICATION Ordinary/Non-Hazardous

Product specifications

MOUNTING STYLE Wall

	Locations
STANDARDS TYPE	NEC/CEC
NEMA RATING	4
INGRESS PROTECTION (IP) RATINGS	IP66

MATERIAL	Galvanized steel
-----------------	------------------

Resources	
3D CAD DRAWING PACKAGE	Eaton Crouse-Hinds V65W-G 3D drawing
3D MODELS	SP3D Design Package - V-Spring Telescoping Safety Light Pole
BROCHURES	Crouse-Hinds series V-Spring Telescoping Safety Light Pole brochure
CATALOGS	Crouse-Hinds series V-Spring Telescoping Safety Light Pole catalog page
CERTIFICATION REPORTS	V-Spring Telescoping Safety Light Pole Canadian certification
INSTALLATION INSTRUCTIONS	IF 1762 - V-Spring Telescoping Safety Light Pole
SPECIFICATIONS AND DATASHEETS	V-Spring Telescoping Safety Light Pole Eaton Specification Sheet - V65W-G

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.



Specifications



Photo is representative

Eaton V65W-G

Eaton Crouse-Hinds series V-Spring telescoping light pole, Galvanized steel, Wall mount

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series V-Spring telescoping light pole
CATALOG NUMBER	V65W-G
UPC	662276470019
PRODUCT LENGTH/DEPTH	73.5 in
PRODUCT HEIGHT	6.57 in
PRODUCT WIDTH	6.57 in
PRODUCT WEIGHT	53 lb



Certifications and compliances

AREA CLASSIFICATION Ordinary/Non-Hazardous

Product specifications

MOUNTING STYLE Wall

	Locations
STANDARDS TYPE	NEC/CEC
NEMA RATING	4
INGRESS PROTECTION (IP) RATINGS	IP66

MATERIAL	Galvanized steel
-----------------	------------------

Resources	
3D CAD DRAWING PACKAGE	Eaton Crouse-Hinds V65W-G 3D drawing
3D MODELS	SP3D Design Package - V-Spring Telescoping Safety Light Pole
BROCHURES	Crouse-Hinds series V-Spring Telescoping Safety Light Pole brochure
CATALOGS	Crouse-Hinds series V-Spring Telescoping Safety Light Pole catalog page
CERTIFICATION REPORTS	V-Spring Telescoping Safety Light Pole Canadian certification
INSTALLATION INSTRUCTIONS	IF 1762 - V-Spring Telescoping Safety Light Pole
SPECIFICATIONS AND DATASHEETS	V-Spring Telescoping Safety Light Pole Eaton Specification Sheet - V65W-G

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.

