

# Specifications



Photo is representative

## Eaton V65W-G

Eaton Crouse-Hinds series V-Spring telescoping light pole, Galvanized steel, Wall mount

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series V-Spring telescoping light pole
<b>CATALOG NUMBER</b>	V65W-G
<b>UPC</b>	662276470019
<b>PRODUCT LENGTH/DEPTH</b>	73.5 in
<b>PRODUCT HEIGHT</b>	6.57 in
<b>PRODUCT WIDTH</b>	6.57 in
<b>PRODUCT WEIGHT</b>	53 lb



### Certifications and compliances

**AREA CLASSIFICATION** Ordinary/Non-Hazardous

### Product specifications

**MOUNTING STYLE** Wall

	Locations
<b>STANDARDS TYPE</b>	NEC/CEC
<b>NEMA RATING</b>	4
<b>INGRESS PROTECTION (IP) RATINGS</b>	IP66

<b>MATERIAL</b>	Galvanized steel
-----------------	------------------

<b>Resources</b>	
<b>3D CAD DRAWING PACKAGE</b>	<a href="#">Eaton Crouse-Hinds V65W-G 3D drawing</a>
<b>3D MODELS</b>	<a href="#">SP3D Design Package - V-Spring Telescoping Safety Light Pole</a>
<b>BROCHURES</b>	<a href="#">Crouse-Hinds series V-Spring Telescoping Safety Light Pole brochure</a>
<b>CATALOGS</b>	<a href="#">Crouse-Hinds series V-Spring Telescoping Safety Light Pole catalog page</a>
<b>CERTIFICATION REPORTS</b>	<a href="#">V-Spring Telescoping Safety Light Pole Canadian certification</a>
<b>INSTALLATION INSTRUCTIONS</b>	<a href="#">IF 1762 - V-Spring Telescoping Safety Light Pole</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">V-Spring Telescoping Safety Light Pole</a> <a href="#">Eaton Specification Sheet - V65W-G</a>

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

