

# Eaton V48M28T12EE

Catalog Number: V48M28T12EE

Eaton General purpose ventilated transformer, DT-3 (3-phase), PV 480V, Taps: 2 at +2.5% /4 at -2.5%, SV 208Y/120V, 150°C rise w/ 200°C insulation system, 112.5 kVA, EE



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton General purpose ventilated transformer	V48M28T12EE
	UPC
	786680019371
<b>Product Length/Depth</b>	<b>Product Height</b>
23.42 in	32.02 in
<b>Product Width</b>	<b>Product Weight</b>
28.22 in	793 lb
<b>Warranty</b>	<b>Compliances</b>
Eaton Selling Policy 25-000, one (1) year NEMA TP-1 Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	
	<b>Certifications</b>
	UL Listed
	<b>Catalog Notes</b>
	NEMA TP-1 efficient

## Physical Attributes

### Coil material

Aluminum

### Frame

916A

### Tap size

2 at +2.5% FCAN, 4 at -2.5% FCBN

### Type

Dry Type Distribution Transformer

## Performance Ratings

### Frequency rating

60 Hz

### Primary voltage

480 V

### Secondary Voltage

208 Y/120 V

### Temperature rise

150 °C rise

### Volt ampere rating

112.5 kVA

## Miscellaneous

### Weathershield

WS19

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - V48M28T12EE](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton V48M28T12EE

Catalog Number: V48M28T12EE

Eaton General purpose ventilated transformer, DT-3 (3-phase), PV 480V, Taps: 2 at +2.5% /4 at -2.5%, SV 208Y/120V, 150°C rise w/ 200°C insulation system, 112.5 kVA, EE



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton General purpose ventilated transformer	V48M28T12EE
	UPC
	786680019371
<b>Product Length/Depth</b>	<b>Product Height</b>
23.42 in	32.02 in
<b>Product Width</b>	<b>Product Weight</b>
28.22 in	793 lb
<b>Warranty</b>	<b>Compliances</b>
Eaton Selling Policy 25-000, one (1) year NEMA TP-1 Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	
	<b>Certifications</b>
	UL Listed
	<b>Catalog Notes</b>
	NEMA TP-1 efficient

## Physical Attributes

### Coil material

Aluminum

### Frame

916A

### Tap size

2 at +2.5% FCAN, 4 at -2.5% FCBN

### Type

Dry Type Distribution Transformer

## Performance Ratings

### Frequency rating

60 Hz

### Primary voltage

480 V

### Secondary Voltage

208 Y/120 V

### Temperature rise

150 °C rise

### Volt ampere rating

112.5 kVA

## Miscellaneous

### Weathershield

WS19

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - V48M28T12EE](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)